

MasterConnect T8

14.5T8/48-850/MF21/MC IA 10/1

MasterConnect, LEDtube, T8, 47-1/4 inch, 14.5 W, 5000 K, 2100 lm, 70000 hour(s)

MasterConnect, LEDtube, T8, 47-1/4 inch, 14.5 W, 5000 K, 2100 lm, 70000 hour(s), 144.00 lm/W, G13 Rotatable end-cap, Plastic

Product data

General Information	
Cap-Base	G13 Rotatable end-cap
Nominal lifetime	70,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	850 [CCT of 5000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,100 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	144.00 lm/W
Color Consistency	<5
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	14.5 W

Lamp Current (Max)	125 mA
Lamp Current (Min)	59 mA
Wattage Equivalent	32 W
Starting Time (Nom)	1 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B
Temperature	
T-Case Maximum (Nom)	113 °F
Controls and Dimming	
Dimmable	Wireless Dim
Connectivity	Interact Ready
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	47-1/4 inch
Bulb Shape	T8

MasterConnect T8

Net Weight (Piece)	0.485 lb
--------------------	----------

Approval and Application


Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Product Data	
Order product name	14.5T8/48-850/MF21/MC IA 10/1
Full product name	14.5T8/48-850/MF21/MC IA 10/1
Order code	562751
Material Nr. (12NC)	929002456804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677562755
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677562750

Dimensional drawing




Product	D1	D2	A1	A2	A3
14.5T8/48-850/MF21/MC IA 10/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data




General uniform lighting - 14.5T8/48-850/MF21/MC IA 10/1




Spectral Power Distribution Colour - 14.5T8/48-850/MF21/MC IA 10/1

Photometric data




Light Distribution Diagram - 14.5T8/48-850/MF21/MC IA 10/1


Lifetime




Lumen Maintenance Diagram - 14.5T8/48-850/MF21/MC IA 10/1



Life Expectancy Diagram




LEDtube_70K_LifetimeVsTc-LED



LEDtube_70K_FailureRate-LED

MasterConnect T8

Lifetime



Lumen Maintenance Diagram - 14.5T8/48-850/MF21/MC IA 10/1

