



# Classic LEDspotLV

## LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10

LEDspotLV Classic offers an archetypal halogen-like design while delivering the benefits of LED technology, saving around 85% on energy consumption, minimizing maintenance cost, and much more besides. It is compatible with most existing fixtures with a GU 5.3 holder and is designed as a retrofit replacement for halogen or incandescent spots.

### Product data

General Information	
Cap-Base	GU5.3
Nominal lifetime	25,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	25,000 h
Lighting Technology	LED
Light Technical	
Color Code	940 [CCT of 4000K]
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	60 degree(s)
Luminous Flux	745 lm
Luminous Intensity (Nom)	770 cd
Color Designation	Cool White (CW)
Luminous Efficacy (rated) (Nom)	99 lm/W
Correlated Color Temperature (Nom)	4000 K
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Input Frequency	- Hz
Power Consumption	7.5 W
Lamp Current (Nom)	660 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	ac electronic 12 V

Temperature	
Ambient temperature range	-20 to +40 °C
T-Case Maximum (Nom)	95 °C

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	MR16

# Classic LEDspotLV

## Approval and Application


Suitable For Accent Lighting	Yes
Energy Consumption kWh/1000 h	9 kWh
EU RoHS compliant	Yes
EyeComfort	No

## Product Data

Order product name	LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10
Full product name	LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10
Full product code	871951435765500

Local code description	LCD84060DMR16
Order code	929002493709
Material Nr. (12NC)	929002493709
Local order code	LCD84060DMR16
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.050 kg
EAN/UPC - Product/Case	8719514357655
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514357662


## Dimensional drawing




## Product

LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10

## Photometric data




Spectral Power Distribution Colour - LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10



Light Distribution Diagram - LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10


# Classic LEDspotLV

## Photometric data



## Accent Lighting Spots - LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10

## Lifetime



## Life Expectancy Diagram

## Lumen Maintenance Diagram - LEDspots 7.5-50W MR16 940 DIM 60D 1PF/10

