



CorePro LED linear MV

CorePro LED linear R7S 118mm 7.2-60W 840

CorePro, LEDspot, R7S, 60 W, R7s, 4000 K, 850 lm, CRI 80, 15000 hour(s), Plastic

CorePro, LEDspot, R7S, 60 W, R7s, 4000 K, 850 lm, CRI 80, 15000 hour(s), Plastic, 118.00 lm/W, EEL E, PF 0.5, RGO, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	R7s
Nominal lifetime	15,000 hour(s)
Switching Cycle	8,000
Lighting Technology	LEDspot
Flux measurement reference	Sphere
Warranty period	2 years
Light Technical	
Color Code	840 [CCT of 4000K]
Luminous Flux	850 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	118.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RGO

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7.2 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	230 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear

CorePro LED linear MV

Bulb Material	Plastic
Bulb Shape	R7S
Net Weight (Piece)	0.035 lb

Approval and Application


Energy Efficiency Class	E
Suitable For Accent Lighting	No
Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	624211
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-4 to +104 °F

Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data


Order product name	CorePro R7S 118mm 7.2-60W 840
Full product name	CorePro LED linear R7S 118mm 7.2-60W 840
Full product code	871951430399700
Order code	371153
Material Nr. (12NC)	929002495102
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514303997
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514304000

Dimensional drawing




Product	D	C
CorePro R7S 118mm 7.2-60W 840	5/8 inch	4-11/16 inch

Photometric data




Spectral Power Distribution Colour - CorePro R7S 118mm 7.2-60W 840



General uniform lighting - CorePro R7S 118mm 7.2-60W 840

CorePro LED linear MV

Photometric data




Light Distribution Diagram - CorePro R7S 118mm 7.2-60W 840

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro R7S 118mm 7.2-60W 840

