



LED Highbay

LED highbay sensor accessory

Philips LED high bay lamps are a direct replacement for 250W to 400W metal halide lamps which will deliver substantial energy savings. Philips LED HighBays delivers bright, clean light for a fraction of the energy used by conventional HID.

Product data

General Information	
Nominal lifetime	50,000 hour(s)
Lighting Technology	LED
Light Technical	
Correlated Color Temperature (Nom)	-
Color Consistency	-
Color rendering index (CRI)	-
Operating and Electrical	
Line Frequency	- Hz
Input Frequency	- Hz
Voltage (Nom)	4-12 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Net Weight (Piece)	0.038 kg

Approval and Application	
EU RoHS compliant	Yes
Ambient temperature range	-20 °C to 45 °C
Application Conditions	
can it be used in closed luminaires	No
Product Data	
Order product name	LED highbay sensor accessory
Full product name	LED highbay sensor accessory
Order code	929002497104
Material Nr. (12NC)	929002497104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677564018
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677564013