



# CorePro Plastic LEDcandles & lusters



## CorePro candle ND 5-40W E14 865 B35 FR

The CorePro LEDcandles and lusters are designed for retrofit replacement of incandescent lamps and are particularly attractive for chandeliers. They are compatible with fixtures with an E14 holder for candles and E14 or E27 holders for lusters and are available in multiple color temperatures. LED lamps deliver huge energy savings of up to 80% energy-saving compared with halogen lamps and provide excellent quality of light. By offering a lifetime of 15,000 hours it lowers maintenance costs. The CorePro LED candles and lusters are perfect for your basic lighting needs.

### Product data


General Information	
Cap-Base	E14
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	865 [CCT of 6500K]
Luminous Flux	470 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K
Luminous Efficacy (rated) (Nom)	94.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG1

Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	5 W
Lamp Current (Nom)	44 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.51
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	81 °C
Controls and Dimming	
Dimmable	No

CorePro Plastic LEDcandles & lusters

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Shape	B35
Net Weight (Piece)	0.040 kg
Approval and Application	
Energy Efficiency Class	F
Energy Consumption kWh/1000 h	5 kWh
EPREL Registration Number	453201
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4
Application Conditions	
can it be used in closed luminaires	No



Dimensional drawing



Product Data	
Order product name	CorePro candle ND 5-40W E14 865 B35 FR
Full product name	CorePro candle ND 5-40W E14 865 B35 FR
Full product code	871951431258600
Order code	929002969202
Material Nr. (12NC)	929002969202
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514312586
Numerator - Packs per outer box	10
EAN/UPC - Case	8719514312593

Product	D	C
CorePro candle ND 5-40W E14 865 B35 FR	35 mm	106 mm

Photometric data




Spectral Power Distribution Colour - CorePro candle ND 5-40W E14 865 B35 FR

General uniform lighting - CorePro candle ND 5-40W E14 865 B35 FR

# CorePro Plastic LEDcandles & lusters

## Photometric data




Light Distribution Diagram - CorePro candle ND 5-40W E14 865 B35 FR

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro candle ND 5-40W E14 865 B35 FR

