



Classic filament LEDbulbs

LED giant crystal 26W E27 smoky DIM

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
Light Technical	
Color Code	818 [CCT of 1800K]
Color Code	818 [CCT of 1800K]
Luminous Flux	270 lm
Luminous Efficacy (rated) (Nom)	38 lm/W
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM) - Flickering value as per	1
EN 61000-3-3	
Stroboscopic effect visibility measure (SVM)	0.4


Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	7 W
Lamp Current (Nom)	43 mA
Wattage Equivalent	26 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C
Controls and Dimming	
Dimmable	Only with specific dimmers

Classic filament LEDbulbs

Mechanical and Housing	
Bulb Finish	smoky
Bulb Material	Glass
Bulb Shape	Crystal
Approval and Application	
Energy Consumption kWh/1000 h	7 kWh
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Application Conditions	
can it be used in closed luminaires	No



Product Data	
Order product name	LED giant crystal 26W E27 smoky DIM
Full product name	LED giant crystal 26W E27 smoky DIM
Full product code	871951431374300
Order code	929002982401
Material Nr. (12NC)	929002982401
Numerator - Quantity Per Pack	1
Net Weight (Piece)	0.494 kg
EAN/UPC - Product/Case	8719514313743
Numerator - Packs per outer box	2
EAN/UPC - Case	8719514313750

Dimensional drawing



Product	D	C
LED giant crystal 26W E27 smoky DIM	103 mm	366 mm

Photometric data




Spectral Power Distribution Colour - LED giant crystal 26W E27 smoky DIM

General uniform lighting - LED giant crystal 26W E27 smoky DIM

Classic filament LEDbulbs

Photometric data



Light Distribution Diagram - LED giant crystal 26W E27 smoky DIM

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED giant crystal 26W E27 smoky DIM

