

Classic filament LEDbulbs

LED classic 25W ST64 E27GOLD SP D RFSRT4

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information	
Cap-Base	E27 [E27]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Rated Lifetime (Hours)	15,000 hour(s)
Lighting Technology	LED
EU RoHS compliant	Yes
Light Technical	
Color Code	818 [CCT of 1800K]
Color Code	818 [CCT of 1800K]
Beam Angle (Nom)	330 degree(s)
Luminous Flux	250 lm
Color Designation	1800
Correlated Color Temperature (Nom)	1800 K
Luminous Efficacy (rated) (Nom)	62 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Flickering value (PstLM)	1

Stroboscopic effect value (SVM)	0.4
Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	4 W
Lamp Current (Nom)	24 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	35 °C

Classic filament LEDbulbs

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------

Mechanical and Housing

Bulb Finish	Amber
Bulb Material	Glass
Bulb Shape	ST64

Approval and Application


Energy Consumption kWh/1000 h	4 kWh
EyeComfort	Yes

Product Data

Order product name	LED classic 25W ST64 E27GOLD SP D RFSRT4
--------------------	---



Full product name	LED classic 25W ST64 E27GOLD SP D RFSRT4
Full product code	871951431545700
Order code	929002982901
Material Nr. (12NC)	929002982901
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514315457
Numerator - Packs per outer box	4
EAN/UPC - Case	8719514315464

Dimensional drawing



Product	D	C
LED classic 25W ST64 E27GOLD SP D RFSRT4	65 mm	143 mm

Photometric data




Spectral Power Distribution Colour - LED classic 25W ST64 E27GOLD SP D RFSRT4

Light Distribution Diagram - LED classic 25W ST64 E27GOLD SP D RFSRT4

Classic filament LEDbulbs

Photometric data




Technical Parameters 43 Philips Lighting B.V. Page 117

General uniform lighting - LED classic 25W ST64 E27GOLD SP D RFSRT4

Lifetime



Life Expectancy Diagram - LED classic 25W ST64 E27GOLD SP D RFSRT4



Lumen Maintenance Diagram - LED classic 25W ST64 E27GOLD SP D RFSRT4

