




Classic filament LED bulbs

5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

LEDbulb, A19, 40 W, E26, 2700 K, 500 lm, 15000 hour(s), Glass

LEDbulb, A19, 40 W, E26, 2700 K, 500 lm, 15000 hour(s), Glass, 90 lm/W

Product data


General Information			
Cap-Base	E26	Wattage Equivalent	40 W
Nominal lifetime	15,000 hour(s)	Starting Time (Nom)	0.5 s
Switching Cycle	20,000	Warm-up time to 60% light	0.5 s
Lighting Technology	LEDbulb	Power Factor (Fraction)	0.7
		Voltage (Nom)	120 V
Light Technical		Controls and Dimming	
Color Code	927 [CCT of 2700K]	Dimmable	Only with specific dimmers
Beam Angle (Nom)	330 degree(s)		
Luminous Flux	500 lm	Mechanical and Housing	
Color Designation	Warm White (WW)	Bulb Finish	Clear
Correlated Color Temperature (Nom)	2700 K	Bulb Material	Glass
Luminous Efficacy (rated) (Nom)	90 lm/W	Bulb Shape	A19
Color Consistency	<4	UL Wet/ damp/ dry location	Wet location
Color rendering index (CRI)	90	Net Weight (Piece)	0.062 lb
LLMF At End Of Nominal Lifetime (Nom)	70 %		
Operating and Electrical		Approval and Application	
Input Frequency	60 Hz	EU RoHS compliant	Yes
Power Consumption	5.5 W	T20 compliant	Yes
Lamp Current (Nom)	62 mA	Ambient temperature range	-4 to +113 °F

Classic filament LED bulbs

Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20
Full product name	5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20
Order code	565788


Material Nr. (12NC)	929002988503
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565787
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565782

Dimensional drawing




Product	D	C
5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20	2-3/8 inch	4-3/16 inch


Photometric data



Spectral Power Distribution Colour - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20




General uniform lighting - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20




Light Distribution Diagram - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

Classic filament LED bulbs

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5.5A19/VIN/927/E26/CL/G/SP DIM 1PF T20

