

LED Designer Deco

5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20

LEDbulb, ST19, 60 W, E26, 5000 K, 500 lm, 15000 hour(s), Glass

LEDbulb, ST19, 60 W, E26, 5000 K, 500 lm, 15000 hour(s), Glass, 90 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	330 degree(s)
Luminous Flux	500 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	90 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	5.5 W
Lamp Current (Nom)	62 mA
Wattage Equivalent	60 W


Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	ST19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.097 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	No

LED Designer Deco

Wireless Technology	Not applicable
Product Data	
Order product name	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20
Full product name	5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20
Order code	565812
Material Nr. (12NC)	929002988803


Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565817
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565812

Dimensional drawing




Product	D	C
5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20	2-9/16 inch	5-7/16 inch


Photometric data



General uniform lighting - 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20



Spectral Power Distribution Colour - 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20



Light Distribution Diagram - 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5.5ST19/VIN/950/E26/CL/G/SP D 4/1PF T20

