



A-Shape LED

10A19/LED/927/FR/P/E26/ND 4/2CT

Philips A-shape LED lamps are the LED alternative to standard incandescents. It provides beautiful light and dependable performance you expect from LED at an affordable price.

Product data

General Information		Lamp Current (Nom)	
Cap-Base	E26 [Single Contact Medium Screw]		135 mA
Nominal lifetime	11,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	11,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.5
EU RoHS compliant	Yes	Voltage (Nom)	120 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	185 °F
Color Code	927 [CCT of 2700K]	Controls and Dimming	
Beam Angle (Nom)	150 degree(s)	Dimmable	No
Luminous Flux	800 lm	Mechanical and Housing	
Color Designation	Warm White (WW)	Bulb Finish	Frosted
Correlated Color Temperature (Nom)	2700 K	Bulb Shape	A19 [A 19mm]
Luminous Efficacy (rated) (Nom)	80.00 lm/W	UL Wet/ damp/ dry location	Damp location
Color Consistency	<6	Approval and Application	
Color rendering index (CRI)	90	Energy Certifications	No
LLMF At End Of Nominal Lifetime (Nom)	0.7 %	EyeComfort	Yes
Operating and Electrical		T20 compliant	No
Line Frequency	60 Hz		
Input Frequency	60 Hz		
Power Consumption	10 W		

A-Shape LED

Application Conditions


can it be used in closed luminaires Yes

Product Data

Order product name	10A19/LED/927/FR/P/E26/ND 4/2CT
Full product name	10A19/LED/927/FR/P/E26/ND 4/2CT
Order code	565440



Material Nr. (12NC)	929003004803
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677565442
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677565447

Dimensional drawing




Product	D	C
10A19/LED/927/FR/P/E26/ND 4/2CT	60 mm	104 mm

Photometric data



General uniform lighting - 10A19/LED/927/FR/P/E26/ND 4/2CT



Spectral Power Distribution Colour - 10A19/LED/927/FR/P/E26/ND 4/2CT



Light Distribution Diagram - 10A19/LED/927/FR/P/E26/ND 4/2CT

A-Shape LED

Lifetime



Lumen Maintenance Diagram - 10A19/LED/927/FR/P/E26/ND 4/2CT

Life Expectancy Diagram - 10A19/LED/927/FR/P/E26/ND 4/2CT

