



LED Lamps

LEDBulb 6W B22 930 230V 2PF/3 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

Product data

| General Information | | Wattage Equivalent | |
|---------------------------------------|--------------------|---------------------------|---------------|
| Cap-Base | B22 | | 55 W |
| Nominal lifetime | 25,000 hour(s) | Starting Time (Nom) | 0.5 s |
| Switching Cycle | 50,000 | Warm-up time to 60% light | 0.5 s |
| Rated Lifetime (Hours) | 15,000 hour(s) | Power Factor (Fraction) | 0.5 |
| Lighting Technology | LED | Voltage (Nom) | 220-240 V |
| Light Technical | | Temperature | |
| Color Code | 930 [CCT of 3000K] | Ambient temperature range | -20 to +45 °C |
| Color Code | 930 [CCT of 3000K] | T-Case Maximum (Nom) | 85 °C |
| Beam Angle (Nom) | 200 degree(s) | Controls and Dimming | |
| Luminous Flux | 560 lm | Dimmable | No |
| Luminous Efficacy (rated) (Nom) | 93 lm/W | Mechanical and Housing | |
| Color Designation | White (WH) | Bulb Finish | Frosted |
| Correlated Color Temperature (Nom) | 3000 K | Bulb Material | Plastic |
| Color Consistency | <6 | Bulb Shape | A60 |
| Color rendering index (CRI) | 90 | Approval and Application | |
| LLMF At End Of Nominal Lifetime (Nom) | 70 % | EU RoHS compliant | Yes |
| Operating and Electrical | | EyeComfort | Yes |
| Input Frequency | 50 to 60 Hz | LED Innovations | EyeComfort |
| Power Consumption | 6 W | | |
| Lamp Current (Nom) | 55 mA | | |


LEDLamps

Product Data

| | |
|-------------------------------|----------------------------------|
| Order product name | LEDBulb 6W B22 930 230V 2PF/3 AU |
| Full product name | LEDBulb 6W B22 930 230V 2PF/3 AU |
| Full product code | 871869968794600 |
| Order code | 929003006419 |
| Material Nr. (12NC) | 929003006419 |
| Numerator - Quantity Per Pack | 2 |

| | |
|---------------------------------|---------------|
| Net Weight (Piece) | 0.042 kg |
| EAN/UPC - Product/Case | 8718699687946 |
| Numerator - Packs per outer box | 3 |
| EAN/UPC - Case | 8718699687953 |



Dimensional drawing



Product


LEDBulb 6W B22 930 230V 2PF/3 AU

Photometric data



Spectral Power Distribution Colour - LEDBulb 6W B22 930 230V 2PF/3 AU

Light Distribution Diagram - LEDBulb 6W B22 930 230V 2PF/3 AU



General uniform lighting - LEDBulb 6W B22 930 230V 2PF/3 AU

LEDLamps

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 6W B22 930 230V 2PF/3 AU

