



# LED Lamps

## LEDBulb 10W B22 930 230V 2PF/3 AU

LED Lamps are a perfect fit for general lighting applications. Compatible with most existing fixtures and designed as a retrofit replacement for incandescent and halogen lamps, LED Lamps deliver huge energy savings and minimize maintenance cost

### Product data

General Information	
Cap-Base	B22
Nominal lifetime	25,000 h
Switching Cycle	50,000
Rated Lifetime (Hours)	15,000 h
Lighting Technology	LED
Light Technical	
Color Code	930 [CCT of 3000K]
Color Code	930 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	1,020 lm
Color Designation	White (WH)
Luminous Efficacy (rated) (Nom)	102 lm/W
Correlated Color Temperature (Nom)	3000 K
Color Consistency	<6
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W
Lamp Current (Nom)	85 mA

Wattage Equivalent	83 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	220-240 V
Temperature	
Ambient temperature range	-20 to +45 °C
T-Case Maximum (Nom)	90 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A60
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort


# LEDLamps

## Product Data

Order product name	LEDBulb 10W B22 930 230V 2PF/3 AU
Full product name	LEDBulb 10W B22 930 230V 2PF/3 AU
Full product code	871869968810300
Local code description	EB10A60c830NC2
Order code	929003007619
Material Nr. (12NC)	929003007619
Local order code	EB10A60C830NC2

Numerator - Quantity Per Pack	2
Net Weight (Piece)	0.042 kg
EAN/UPC - Product/Case	8718699688103
Numerator - Packs per outer box	3
EAN/UPC - Case	8718699688110



## Dimensional drawing



## Product


LEDBulb 10W B22 930 230V 2PF/3 AU

## Photometric data



Light Distribution Diagram - LEDBulb 10W B22 930 230V 2PF/3 AU

Spectral Power Distribution Colour - LEDBulb 10W B22 930 230V 2PF/3 AU



General uniform lighting - LEDBulb 10W B22 930 230V 2PF/3 AU

General uniform lighting - LEDBulb 10W B22 930 230V 2PF/3 AU

# LEDLamps

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDBulb 10W B22 930 230V 2PF/3 AU

