



# Classic filament LEDbulbs

## LEDclassic 60W ST64 2700K E27 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data

| General Information                   |                    |
|---------------------------------------|--------------------|
| Cap-Base                              | E27                |
| Nominal lifetime                      | 15,000 h           |
| Switching Cycle                       | 20,000             |
| Rated Lifetime (Hours)                | 15,000 h           |
| Lighting Technology                   | LED                |
| Light Technical                       |                    |
| Color Code                            | 927 [CCT of 2700K] |
| Color Code                            | 927 [CCT of 2700K] |
| Luminous Flux                         | 806 lm             |
| Color Designation                     | Warm White (WW)    |
| Luminous Efficacy (rated) (Nom)       | 134 lm/W           |
| Correlated Color Temperature (Nom)    | 2700 K             |
| Color Consistency                     | <6                 |
| Color rendering index (CRI)           | 90                 |
| LLMF At End Of Nominal Lifetime (Nom) | 70 %               |
| Operating and Electrical              |                    |
| Input Frequency                       | 50 to 60 Hz        |
| Power Consumption                     | 6 W                |
| Lamp Current (Nom)                    | 40 mA              |


| Wattage Equivalent            | 60 W                       |
|-------------------------------|----------------------------|
| Starting Time (Nom)           | 0.5 s                      |
| Warm-up time to 60% light     | 0.5 s                      |
| Power Factor (Fraction)       | 0.6                        |
| Voltage (Nom)                 | 220-240 V                  |
| Temperature                   |                            |
| Ambient temperature range     | -20 to +45 °C              |
| T-Case Maximum (Nom)          | 70 °C                      |
| Controls and Dimming          |                            |
| Dimmable                      | Only with specific dimmers |
| Mechanical and Housing        |                            |
| Bulb Finish                   | Clear                      |
| Bulb Material                 | Glass                      |
| Bulb Shape                    | ST64                       |
| Approval and Application      |                            |
| Energy Consumption kWh/1000 h | 6 kWh                      |
| EU RoHS compliant             | Yes                        |
| EyeComfort                    | Yes                        |

# Classic filament LEDbulbs

|                        |                                       |
|------------------------|---------------------------------------|
| LED Innovations        | EyeComfort                            |
| <b>Product Data</b>    |                                       |
| Order product name     | LEDclassic 60W ST64 2700K E27 D CL AU |
| Full product name      | LEDclassic 60W ST64 2700K E27 D CL AU |
| Full product code      | 871951437721900                       |
| Local code description | FIL60WST64WWESD                       |
| Order code             | 929003010779                          |
| Material Nr. (12NC)    | 929003010779                          |



|                                 |                 |
|---------------------------------|-----------------|
| Local order code                | FIL60WST64WWESD |
| Numerator - Quantity Per Pack   | 1               |
| Net Weight (Piece)              | 0.048 kg        |
| EAN/UPC - Product/Case          | 8719514377219   |
| Numerator - Packs per outer box | 6               |
| EAN/UPC - Case                  | 8719514377226   |

## Dimensional drawing




| Product                               | D     | C      |
|---------------------------------------|-------|--------|
| LEDclassic 60W ST64 2700K E27 D CL AU | 64 mm | 140 mm |

## Photometric data



Spectral Power Distribution Colour - LEDclassic 60W ST64 2700K E27 D CL AU

Light Distribution Diagram - LEDclassic 60W ST64 2700K E27 D CL AU



# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 60W ST64 2700K E27 D CL AU

