

Classic filament LED candles and lusters

LEDclassic 40W B35 2700K E27 D CL AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data


General Information		Power Consumption	
Cap-Base	E27	3.5 W	
Nominal lifetime	15,000 h	Lamp Current (Nom)	
Switching Cycle	20,000	24 mA	
Rated Lifetime (Hours)	15,000 h	Wattage Equivalent	
Lighting Technology	LED	40 W	
Light Technical		Starting Time (Nom)	
Color Code	927 [CCT of 2700K]	0.5 s	
Color Code	927 [CCT of 2700K]	Warm-up time to 60% light	
Luminous Flux	470 lm	0.5 s	
Color Designation	Warm White (WW)	Power Factor (Fraction)	
Correlated Color Temperature (Nom)	2700 K	0.6	
Luminous Efficacy (rated) (Nom)	134 lm/W	Voltage (Nom)	
Color Consistency	<6	220-240 V	
Color rendering index (CRI)	90	Temperature	
LLMF At End Of Nominal Lifetime (Nom)	70 %	T-Case Maximum (Nom)	
Operating and Electrical		70 °C	
Input Frequency		Controls and Dimming	
50 to 60 Hz		Dimmable	
		Only with specific dimmers	
		Mechanical and Housing	
		Bulb Finish	
		Clear	
		Bulb Material	
		Glass	
		Bulb Shape	
		B35	
		Net Weight (Piece)	
		0.014 kg	

Classic filament LED candles and lusters

Approval and Application	
Energy Consumption kWh/1000 h	4 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C
Product Data	
Order product name	LEDclassic 40W B35 2700K E27 D CL AU
Full product name	LEDclassic 40W B35 2700K E27 D CL AU
Full product code	871951438462000


Local code description	FIL40WB35WWESD
Order code	929003012379
Material Nr. (12NC)	929003012379
Local order code	FIL40WB35WWESD
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514384620
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514384637

Dimensional drawing




Product	D	C
LEDclassic 40W B35 2700K E27 D CL AU	35 mm	95 mm

Photometric data




General uniform lighting - LEDclassic 40W B35 2700K E27 D CL AU



Light Distribution Diagram - LEDclassic 40W B35 2700K E27 D CL AU


Classic filament LED candles and lusters

Photometric data




Spectral Power Distribution Colour - LEDclassic 40W B35 2700K E27 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 40W B35 2700K E27 D CL AU

