

Classic filament LED candles and lusters

LEDclassic 40W B35 2700K E27 D CL AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information		Power Consumption	
Cap-Base	E27	Lamp Current (Nom)	24 mA
Nominal lifetime	15,000 hour(s)	Wattage Equivalent	40 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	15,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.6
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	70 °C
Color Code	927 [CCT of 2700K]		
Luminous Flux	470 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	134 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	90	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	B35
Operating and Electrical		Net Weight (Piece)	0.014 kg
Input Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

Approval and Application


Energy Consumption kWh/1000 h	4 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	LEDclassic 40W B35 2700K E27 D CL AU
Full product name	LEDclassic 40W B35 2700K E27 D CL AU



Full product code	871951438462000
Order code	929003012379
Material Nr. (12NC)	929003012379
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514384620
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514384637

Dimensional drawing



Product	D	C
LEDclassic 40W B35 2700K E27 D CL AU	35 mm	95 mm

Photometric data




General uniform lighting - LEDclassic 40W B35 2700K E27 D CL AU

Light Distribution Diagram - LEDclassic 40W B35 2700K E27 D CL AU


Classic filament LED candles and lusters

Photometric data




Spectral Power Distribution Colour - LEDclassic 40W B35 2700K E27 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 40W B35 2700K E27 D CL AU

