



Classic filament LED candles and lusters

LEDclassic 40W P45 2700K E14 D CL AU

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

Product data

General Information		Power Consumption	
Cap-Base	E14	Power Consumption	3.5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	24 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Rated Lifetime (Hours)	15,000 hour(s)	Starting Time (Nom)	0.5 s
Lighting Technology	LED	Warm-up time to 60% light	0.5 s
Light Technical		Power Factor (Fraction)	0.6
Color Code	927 [CCT of 2700K]	Voltage (Nom)	220-240 V
Color Code	927 [CCT of 2700K]	Temperature	
Luminous Flux	470 lm	T-Case Maximum (Nom)	70 °C
Color Designation	Warm White (WW)	Controls and Dimming	
Correlated Color Temperature (Nom)	2700 K	Dimmable	Only with specific dimmers
Luminous Efficacy (rated) (Nom)	134 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	90	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	P45
Operating and Electrical		Net Weight (Piece)	0.014 kg
Input Frequency	50 to 60 Hz		

Classic filament LED candles and lusters

Approval and Application


Energy Consumption kWh/1000 h	4 kWh
EU RoHS compliant	Yes
EyeComfort	Yes
LED Innovations	EyeComfort
Ambient temperature range	-20 to +45 °C

Product Data

Order product name	LEDclassic 40W P45 2700K E14 D CL AU
Full product name	LEDclassic 40W P45 2700K E14 D CL AU


Full product code	871951437739400
Order code	929003013179
Material Nr. (12NC)	929003013179
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514377394
Numerator - Packs per outer box	6
EAN/UPC - Case	8719514377400

Dimensional drawing




Product	D	C
LEDclassic 40W P45 2700K E14 D CL AU	45 mm	80 mm

Photometric data




Spectral Power Distribution Colour - LEDclassic 40W P45 2700K E14 D CL AU



Light Distribution Diagram - LEDclassic 40W P45 2700K E14 D CL AU


Classic filament LED candles and lusters

Photometric data




General uniform lighting - LEDclassic 40W P45 2700K E14 D CL AU

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LEDclassic 40W P45 2700K E14 D CL AU

