



# MASTER Value Glass LED bulbs

## MASTER VLE LEDBulb D7.8-75W E27 927 A60 FRG

Featuring a classic heritage design, these filament LED bulbs combine the familiar shapes of incandescent bulbs with the benefits of long-lasting LED technology. These MASTER Value Glass LED bulbs offer more energy savings than normal glass LED bulbs. At the same time, they also provide customers with good light experience, enhanced by excellent dimming performance (dimmable glass LED bulbs). MASTER Value Glass LED Bulbs deliver significant energy savings, using 30% less energy compared to normal LED bulbs and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED bulbs also reduce maintenance costs.

### Product data


General Information		Operating and Electrical	
Cap base	E27	Colour consistency	<6
Nominal lifetime	15,000 h	Colour rendering index (CRI)	90
Switching Cycle	20,000	LLMF at end of nominal lifetime (nom.)	70 %
Lighting Technology	LED	Photobiological safety according to EN 62471 RGO	
Flux measurement reference	Sphere		
Light Technical			
Colour Code	927 [CCT of 2700K]	Line Frequency	50 to 60 Hz
Beam angle (nom.)	300 degree(s)	Input frequency	50 to 60 Hz
Luminous Flux	1,055 lm	Power Consumption	7.8 W
Colour designation	Warm White (WW)	Lamp current (nom.)	46 mA
Correlated Colour Temperature (Nom)	2700 K	Wattage equivalent	75 W
Luminous efficacy (rated) (nom.)	135.00 lm/W	Starting time (nom.)	0.5 s
		Warm-up time to 60% light	0.5 s
		Power Factor (Fraction)	0.7

MASTER Value Glass LED bulbs

Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Frosted
Bulb shape	A60
Net Weight (Piece)	0.030 kg
Approval and Application	
Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	574364
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes



Flickering value (PstLM)	1
Stroboscopic effect	0.4
Application Conditions	
Can it be used in closed luminaires	No
Product Data	
Order product name	MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG
Full product name	MASTER VLE LEDBulb D7.8-75W E27 927 A60 FRG
Full EOC	871951434790800
Order code	34790800
Material no. (12 NC)	929003058102
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514347908
Numerator – packs per outer box	10
EAN/UPC - Case	8719514347915

Dimensional drawing



Product	D	C
MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG	60 mm	104 mm

Photometric data




Spectral Power Distribution Colour - MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG

General uniform lighting - MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG

MASTER Value Glass LED bulbs

Photometric data




Light Distribution Diagram - MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS VLE LEDBulb D7.8-75W E27 927 A60 FRG

