

# Classic filament LEDbulbs

## LEDclassic 60W E27 2700K G120 D CL AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.

### Product data


General Information		Lamp Current (Nom)	
Cap-Base	E27		35 mA
Nominal lifetime	15,000 h	Wattage Equivalent	60 W
Switching Cycle	20,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	15,000 h	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.7
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	927 [CCT of 2700K]	T-Case Maximum (Nom)	80 °C
Color Code	927 [CCT of 2700K]		
Luminous Flux	806 lm	Controls and Dimming	
Color Designation	Warm White (WW)	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	2700 K		
Luminous Efficacy (rated) (Nom)	134 lm/W	Mechanical and Housing	
Color Consistency	<6	Bulb Finish	Clear
Color rendering index (CRI)	90	Bulb Material	Glass
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Shape	G120
Photobiological safety according to EN 62471	RGO	Net Weight (Piece)	0.165 kg
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	6 kWh
Power Consumption	6 W	EU RoHS compliant	Yes

# Classic filament LEDbulbs

Ambient temperature range	-20 to +45 °C
<b>Product Data</b>	
Order product name	LEDclassic 60W E27 2700K G120 D CL AU
Full product name	LEDclassic 60W E27 2700K G120 D CL AU
Full product code	871951438588700
Local code description	FIL60WG120WWESD
Order code	929003059379



Material Nr. (12NC)	929003059379
Local order code	FIL60WG120WWESD
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514385887
Numerator - Packs per outer box	3
EAN/UPC - Case	8719514385894

## Dimensional drawing




Product	D	C
LEDclassic 60W E27 2700K G120 D CL AU	124 mm	178 mm

## Photometric data



Spectral Power Distribution Colour - LEDclassic 60W E27 2700K G120 D CL AU


General uniform lighting - LEDclassic 60W E27 2700K G120 D CL AU



Light Distribution Diagram - LEDclassic 60W E27 2700K G120 D CL AU

# Classic filament LEDbulbs

## Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - LEDclassic 60W E27 2700K G120 D CL AU

