



MASTER Value GLASS LED candles and lustres

MAS VLE LEDLusterD3.4-40W E27 P45 927CLG

MASTER Value, LEDbulb, P45, 40 W, E27, 2700 K, 470 lm, CRI 90, 15000 h, Glass

MASTER Value Glass LED lustres feature a classic heritage design, these filament LED lamps combine the familiar shapes of incandescent candles and lustres with the benefits of long-lasting LED technology. These glass LED lustres offer more energy savings than normal LED candles and lustres. At the same time, they also provide customers with a good light experience, enhanced by excellent dimming performance (dimnable LED candles). MASTER Value Glass LED lustres deliver significant energy savings, using 30% less energy compared to normal glass LED candles and provide excellent quality of light. By offering a lifetime of 15,000 hours, these dimmable LED candles and lustres also reduce maintenance costs.


Product data

General Information			
Cap base	E27	Beam angle (nom.)	300 degree(s)
Nominal lifetime	15,000 h	Luminous Flux	470 lm
Switching Cycle	20,000	Colour designation	Warm White (WW)
Lighting Technology	LEDbulb	Correlated Colour Temperature (Nom)	2700 K
Flux measurement reference	Sphere	Luminous efficacy (rated) (nom.)	138.00 lm/W
		Colour consistency	<6
		Colour rendering index (CRI)	90
		LLMF at end of nominal lifetime (nom.)	70 %
Light Technical			
Colour Code	927 [CCT of 2700K]		

MASTER Value GLASS LED candles and lustres

Photobiological safety according to EN 62471 RGO	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	3.4 W
Lamp current (nom.)	20 mA
Wattage equivalent	40 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	80 °C
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Lamp Finish	Clear
Bulb material	Glass
Bulb shape	P45
Net Weight (Piece)	0.014 kg
Approval and Application	
Energy Efficiency Class	D

Dimensional drawing



Energy consumption kWh/1,000 hours	4 kWh
EPREL Registration Number	574373
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C

Application Conditions

Can it be used in closed luminaires	No
-------------------------------------	----

Product Data

Order product name	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG
Full product name	MAS VLE LEDLusterD3.4-40W E27 P45 927CLG
Full EOC	871951435551400
Order code	929003060402
Material no. (12 NC)	929003060402
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514355514
Numerator – packs per outer box	10
EAN/UPC – Case	8719514355521

Product	D	C
MAS VLE LEDLusterD3.4-40W E27 P45 927CLG	45 mm	78 mm

MASTER Value GLASS LED candles and lustres

