



TrueForce High Lumen PAR

27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB

LEDspot, PAR38, 250 W, E26, 3000 K, 2800 lm, 25000 hour(s), Aluminum

LEDspot, PAR38, 250 W, E26, 3000 K, 2800 lm, 25000 hour(s), Aluminum, 103.00 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	15 degree(s)
Luminous Flux	2,800 lm
Luminous Intensity (Nom)	18,000 cd
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	103.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Line Frequency	60 Hz
Input Frequency	60 Hz
Power Consumption	27 W
Lamp Current (Nom)	216 mA
Wattage Equivalent	250 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	167 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear

TrueForce High Lumen PAR

Bulb Material	Aluminum
Bulb Shape	PAR38
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.937 lb

Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	N/A
Ambient temperature range	-4 to +113 °F

Application Conditions


can it be used in closed luminaires	No
-------------------------------------	----

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB
Full product name	27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB
Order code	569723
Material Nr. (12NC)	929003063504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677569723
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677569728

Dimensional drawing




Product	D	C
27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB	4-3/4 inch	5-3/16 inch

Photometric data




Light Distribution Diagram - 27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB



Accent Lighting Spots - 27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB


TrueForce High Lumen PAR

Photometric data




Spectral Power Distribution Colour - 27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 27PAR38TrueF 830 F15 DIM 120V-277V 6/1FB

