



# Classic filament LEDbulbs

## LED CLA 60W A60 E27 3000K CL EELA SRT AU

Featuring a classic heritage design, LED Deco Classic delivers beautiful, decorative warm-white light while saving around 90% on energy costs.


### Product data

General Information		Lamp Current (Nom)	
Cap-Base	E27		45 mA
Nominal lifetime	50,000 hour(s)	Wattage Equivalent	60 W
Switching Cycle	50,000	Starting Time (Nom)	0.5 s
Rated Lifetime (Hours)	50,000 hour(s)	Warm-up time to 60% light	0.5 s
Lighting Technology	LED	Power Factor (Fraction)	0.4
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Color Code	830 [CCT of 3000K]	Ambient temperature range	-20 to +45 °C
Color Code	830 [CCT of 3000K]	T-Case Maximum (Nom)	35 °C
Luminous Flux	840 lm		
Luminous Efficacy (rated) (Nom)	210 lm/W	Controls and Dimming	
Color Designation	White (WH)	Dimmable	No
Correlated Color Temperature (Nom)	3000 K		
Color Consistency	<6	Mechanical and Housing	
Color rendering index (CRI)	80	Bulb Finish	Clear
LLMF At End Of Nominal Lifetime (Nom)	70 %	Bulb Material	Glass
Photobiological safety according to EN 62471	RG1	Bulb Shape	A60
Operating and Electrical		Approval and Application	
Input Frequency	50 to 60 Hz	Energy Consumption kWh/1000 h	- kWh
Power Consumption	4 W	EU RoHS compliant	Yes



# Classic filament LEDbulbs

## Photometric data



Light Distribution Diagram - LED CLA 60W A60 E27 3000K CL EELA SRT AU

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - LED CLA 60W A60 E27 3000K CL EELA SRT AU

