



LED Designer Deco

1S14/VIN/827/CL/G/E26/ND 1CT

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data


General Information	
Cap-Base	E26 [Single Contact Medium Screw]
Nominal lifetime	15,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LED
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	60 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	60.00 lm/W
Color Consistency	<4
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	1 W
Lamp Current (Nom)	12 mA
Wattage Equivalent	10 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5

Voltage (Nom)	110-130 V
Temperature	
T-Case Maximum (Nom)	26 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Bulb Shape	S-14
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.016 kg
Approval and Application	
Energy Certifications	No
EU RoHS compliant	Yes
T20 compliant	Yes
Application Conditions	
can it be used in closed luminaires	Yes
Product Data	
Order product name	1S14/VIN/827/CL/G/E26/ND 1CT

Full product name	1S14/VIN/827/CL/G/E26/ND 1CT
Order code	929003082704
Material Nr. (12NC)	929003082704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677575205


Numerator - Packs per outer box	10
EAN/UPC - Case	50046677575200

Dimensional drawing




Product	D	C
1S14/VIN/827/CL/G/E26/ND 1CT	45 mm	86 mm


Photometric data



Spectral Power Distribution Colour - 1S14/VIN/827/CL/G/E26/ND 1CT




Light Distribution Diagram - 1S14/VIN/827/CL/G/E26/ND 1CT




General uniform lighting - 1S14/VIN/827/CL/G/E26/ND 1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 1S14/VIN/827/CL/G/E26/ND 1CT

