



LED Designer Deco

1S14/VIN/827/CL/G/E26/ND 1CT

LEDbulb, S-14, 10 W, E26, 2700 K, 60 lm, 15000 hour(s), Glass

Philips LED Designer Deco lamps allow you to maintain a warm, classic light or a modern, chic effect while providing longer life and energy savings

Product data

General Information		Starting Time (Nom)		0.5 s
Cap-Base	E26	Warm-up time to 60% light		0.5 s
Nominal lifetime	15,000 hour(s)	Power Factor (Fraction)		0.5
Switching Cycle	20,000	Voltage (Nom)		110-130 V
Lighting Technology	LEDbulb			
Light Technical		Temperature		
Color Code	827 [CCT of 2700K]	T-Case Maximum (Nom)		79 °F
Luminous Flux	60 lm	Controls and Dimming		
Color Designation	Warm White (WW)	Dimmable		No
Correlated Color Temperature (Nom)	2700 K	Mechanical and Housing		
Luminous Efficacy (rated) (Nom)	60.00 lm/W	Bulb Finish		Clear
Color Consistency	<4	Bulb Material		Glass
Color rendering index (CRI)	80	Bulb Shape		S-14
LLMF At End Of Nominal Lifetime (Nom)	70 %	UL Wet/ damp/ dry location		Wet location
Operating and Electrical		Net Weight (Piece)		0.035 lb
Line Frequency	50 to 60 Hz	Approval and Application		
Input Frequency	50 to 60 Hz	Energy Certifications		No
Power Consumption	1 W	EU RoHS compliant		Yes
Lamp Current (Nom)	12 mA	T20 compliant		Yes
Wattage Equivalent	10 W			

LED Designer Deco

Ambient temperature range	-4 to +104 °F
---------------------------	---------------

Application Conditions


can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Product Data

Order product name	1S14/VIN/827/CL/G/E26/ND 1CT
Full product name	1S14/VIN/827/CL/G/E26/ND 1CT


Order code	575209
Material Nr. (12NC)	929003082704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677575205
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677575200

Dimensional drawing




Product	D	C
1S14/VIN/827/CL/G/E26/ND 1CT	1-13/16 inch	3-7/16 inch


Photometric data



Spectral Power Distribution Colour - 1S14/VIN/827/CL/G/E26/ND 1CT




Light Distribution Diagram - 1S14/VIN/827/CL/G/E26/ND 1CT




General uniform lighting - 1S14/VIN/827/CL/G/E26/ND 1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 1S14/VIN/827/CL/G/E26/ND 1CT

