



InstantFit (UL Type-A) T5

24T5HO/COR/46-835/IF33/G/DIM 25/1

CorePro, LEDtube, T5, 47-1/4 inch, 24 W, 3500 K, 3300 lm, 50000 hour(s)

CorePro, LEDtube, T5, 47-1/4 inch, 24 W, 3500 K, 3300 lm, 50000 hour(s), 137.00 lm/W, G5, Glass

Product data

General Information			
Cap-Base	G5	Input Frequency	50 to 60 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	24 W
Switching Cycle	50,000	Lamp Current (Max)	1,200 mA
Lighting Technology	LEDtube	Lamp Current (Min)	30 mA
		Wattage Equivalent	54 W
		Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	835 [CCT of 3500K]	Power Factor (Fraction)	0.9
Beam Angle (Nom)	200 degree(s)	Voltage (Nom)	120-277, 347 V
Luminous Flux	3,300 lm	UL Type	UL Type A
Color Designation	White (WH)		
Correlated Color Temperature (Nom)	3500 K	Temperature	
Luminous Efficacy (rated) (Nom)	137.00 lm/W	T-Case Maximum (Nom)	158 °F
Color Consistency	<6		
Color rendering index (CRI)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	Only with specific dimmers
Operating and Electrical			
Line Frequency	50 to 60 Hz	Mechanical and Housing	
		Bulb Finish	Frosted

InstantFit (UL Type-A) T5

Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T5
Net Weight (Piece)	0.333 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	24T5HO/COR/46-835/IF33/G/DIM 25/1
Full product name	24T5HO/COR/46-835/IF33/G/DIM 25/1
Order code	576710
Material Nr. (12NC)	929003134004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677576714
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677576719

Dimensional drawing



Product	D1	D2	A1	A2	A3
24T5HO/COR/46-835/IF33/G/DIM 25/1	5/8 inch	3/4 inch	45-3/16 inch	45-1/2 inch	45-3/4 inch

Photometric data




General uniform lighting - 24T5HO/COR/46-835/IF33/G/DIM 25/1

Light Distribution Diagram - 24T5HO/COR/46-835/IF33/G/DIM 25/1


InstantFit (UL Type-A) T5

Photometric data




Spectral Power Distribution Colour - 24T5HO/COR/46-835/IF33/G/DIM 25/1


Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 24T5HO/COR/46-835/IF33/G/DIM 25/1




LEDtube 50K 7090 FailureRate-LED



Lumen Maintenance Diagram - 24T5HO/COR/46-835/IF33/G/DIM 25/1

InstantFit (UL Type-A) T5

Lifetime



LifetimeVsTc

