



Magnetic Sys

Mag Tracker Trimless 1M

Magnetic Sys offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance. Also an ideal solution for easy installation and DIY design friendly.

Product data

General Information	
Light source replaceable	No
Driver included	No
Lighting Technology	LED
Warranty period	1 years
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Operating and Electrical	
Input Voltage	48 V
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminium
Reflector material	-
Housing Color	Black
Overall length	1,000 mm

Overall width	75.5 mm
Overall height	53 mm
Dimensions (Height x Width x Depth)	53 x 76 x 1000 mm
Net weight	1.21 kg
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class III
Warranty	3 year(s)
Initial Performance (IEC Compliant)	
Initial chromaticity	(NA) NA
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 hour(s)
Application Conditions	
Suitable for random switching	No
Product Data	
Order product name	Mag Tracker Trimless 1M
Full product name	Mag Tracker Trimless 1M

Magnetic Sys

Full product code	692234195461000
Order code	929003206510
Material Nr. (12NC)	929003206510
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6922341954610

Numerator - Packs per outer box	6
EAN/UPC - Case	6922341954627

Dimensional drawing

