



Magnetic Sys

Mag Tracker Trimless 2M

Magnetic Sys offers excellent experience for the consumer, which includes eye comfort, reliable quality and outstanding performance. Also an ideal solution for easy installation and DIY design friendly.

Product data

General Information	
Light source replaceable	No
Driver included	No
Lighting Technology	LED
Operating and Electrical	
Input Voltage	48 V
Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Constant light output	No
Mechanical and Housing	
Housing Material	Aluminium
Reflector material	-
Housing Color	Black
Overall length	2,000 mm
Overall width	75.5 mm
Overall height	53 mm
Dimensions (Height x Width x Depth)	53 x 76 x 2000 mm

Net weight	2.42 kg
Approval and Application	
Ingress protection code	IP20 [Finger-protected]
Mech. impact protection code	IK03 [0.3 J]
Protection class IEC	Safety class III
Glow-wire test	Temperature 650 °C, duration 30 s
Flammability mark	For mounting on normally flammable surfaces
Warranty period	1 years
EU RoHS compliant	Yes
Warranty	3 year(s)
Initial Performance (IEC Compliant)	
Initial chromaticity	(NA) NA
Power consumption tolerance	+/-10%
Over Time Performance (IEC Compliant)	
Median useful life L70B50	25,000 hour(s)
Application Conditions	
Suitable for random switching	No
Product Data	
Order product name	Mag Tracker Trimless 2M

Magnetic Sys

Full product name	Mag Tracker Trimless 2M
Full product code	692234195463400
Order code	929003206610
Material Nr. (12NC)	929003206610
Numerator - Quantity Per Pack	1
Net Weight (Piece)	2.445 kg

EAN/UPC - Product/Case	6922341954634
Numerator - Packs per outer box	6
EAN/UPC - Case	6922341954641

Dimensional drawing

