







# Wi-Fi BLE Portable Light User Manual

9290032118



## 1. Product introduction

We hope that you enjoy your new WIZ portable light which brings you gradient and pastel lighting, allowing you to create the perfect lighting for focus or relaxation, and to set the perfect ambience just the way you like.

Box contents: Portable light\*1, Power adaptor\*1, User manual\*1, Quick set-up\*1

- ① Touch panel
- ② Housing
- ③ USB type C charging port
- ④ Adaptor

## 2. Usage instructions

⑤ Mode button:

- Mode button is used to change light mode.
- Switch through 4 of your favorite modes: Sync with your WIZ App to set your favorite modes.

⑥ Dimming slider:

- Dim up and down by touching any point of the slider.
- Not applicable to Night Light, Wake-up and Bedtime modes.

⑦ on/off button:

- Press the blue dot button to turn the product on and off.
- While the product is off, press the blue dot button continuously for 10 seconds to enter pairing mode.

⑧ Led indicator:

- Red light indicates low battery.
- Green light indicates that the lamp is charging and ready to use. Green light will be off when fully charged.

⑨ Power switch

## 3. Warnings

Luminaires shall be connected to the supply in compliance with the national standard of the country where the luminaires will be installed. Should you have any doubt, please seek advice from a professional electrician.

Always disconnect from main supply before installation, connection and servicing.

Please use the adaptor provided in the box from the manufacturer.

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

To guarantee optimal battery performance, do not let the product reach a high temperature.

There is built-in rechargeable lithium-ion battery in the product.

Remove the battery from the product before disposing the product.

Dispose the used battery according to local regulations.

Don't use the product if battery is leaking.

Charge the battery with adapter provided with the product.

## 4. Safety instructions

Read carefully all these instructions before assembling and operating and keep these instructions.

To reduce the risk of fire, electrical shocks and personal injuries when using electrical appliances, basic safety precautions should always be followed.

Check if the electrical specifications are compatible.

The product is designed for indoor use only.

The construction is IP20, never use the product in bathroom or close to water points. The Product can be installed in dry premise only.

**Warning: The external flexible cord of this luminaire can not be replaced, if the cord is damaged, the luminaire shall be destroyed.**

## 5. Servicing

### How to clean the product

Clean with a soft dust cloth.

Never use alcohol, solvent or products of a similar nature.

## 6. Symbols explanation



Class III appliance



Class II appliance



Indoor use only

## 7. Warranty

Warranty is subject to strict conditions of use, for more information, please visit our website:

<https://www.wizconnected.com/en/consumer/support/>

Wireless specification:

Wireless RF mode frequency band: 2400 - 2483.5 MHz

Maximum transmitted power:

Wi-Fi: Max 20 dBm

Bluetooth: Max 10 dBm

Products shall not be used with dimmers, for dimming use the WIZ application.

On/off functionality available without Wi-Fi connectivity.

Wi-Fi®, the Wi-Fi CERTIFIED logo are registered trademarks of Wi-Fi Alliance.

Wi-Fi CERTIFIED™, WPA2™ are trademarks of Wi-Fi Alliance.

The Bluetooth® word and logos are registered trademarks owned by Bluetooth SIG, INC.

Amazon, Alexa and all related logos are trademarks of Amazon.com, Inc or its affiliates.

Google is a trademark of Google LLC. Siri is a registered trademark of Apple Inc.

Any use of such marks by Signify is under license.

Other trademarks and trade names are those of their respective owners.