




Wi-Fi BLE Floor Light  
User Manual

9290032125



## 1. Product introduction

Complement your home's decor with the linear and stylish design of the WiZ floor light. The lamp paints any wall with a unique gradient of light.

Versatile in use as the floor lamp can stand vertically and also horizontally behind your TV.

Box contents: Floor Light\*1, Base\*1, Accessory\*1, Power adaptor\*1, User manual\*1, Quick set-up\*1

- ① Power button
- ② Lamp body
- ③ Extender
- ④ Base
- ⑤ Adaptor

## 2. Usage instructions

- Press the power button to turn on and off
- When the light is on, hold the power button down for dimming.
- When the light is off, hold the power button down for 10 seconds to enter pairing mode.



## 3. Warnings

Luminaires shall be connected to the supply in compliance with the national standard of the country where the luminaires will be installed. Should you have any doubt, please seek advice from a professional electrician.

Always disconnect from main supply before installation, connection and servicing.

The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.

## 4. Safety instructions

Read carefully all these instructions before assembling and operating and keep these instructions.

To reduce the risk of fire, electrical shocks and personal injuries when using electrical appliances, basic safety precautions should always be followed.

Check if the electrical specifications are compatible.

The product is designed for indoor use only.

The construction is IP20, never use the product in bathroom or close to water points. The Product can be installed in dry premise only.

Please use the adaptor provided in the box from the manufacturer.

## 5. Servicing

### How to clean the product

Clean with a soft dust cloth.

Never use alcohol, solvent or products of a similar nature.

## 6. Symbols explanation



Class III appliance



Indoor use only



Class II appliance

## 7. Warranty

Warranty is subject to strict conditions of use, for more information, please visit our website:

<https://www.wizconnected.com/en/consumer/support/>

Wireless specification:

Wireless RF mode frequency band: 2400 - 2483.5 MHz

Maximum transmitted power:

Wi-Fi: Max 20 dBm

Bluetooth: Max 10 dBm

Products shall not be used with dimmers, for dimming use the WiZ application.

On/off functionality available without Wi-Fi connectivity.

Wi-Fi\*, the Wi-Fi CERTIFIED logo are registered trademarks of Wi-Fi Alliance.

Wi-Fi CERTIFIED™, WPA2™ are trademarks of Wi-Fi Alliance.

The Bluetooth\* word and logos are registered trademarks owned by Bluetooth SIG, INC.

Amazon, Alexa and all related logos are trademarks of Amazon.com, Inc or its affiliates.

Google is a trademark of Google LLC. Siri is a registered trademark of Apple Inc.

Any use of such marks by Signify is under license.

Other trademarks and trade names are those of their respective owners.