

Contractor-grade MainsFit (UL Type-B) T8

14.5T8/CNG/48-835/MF17/G 25/1

Contractor grade, LEDtube, T8, 47-1/4 inch, 14.5 W, 3500 K, 1750 lm, 50000 hour(s)

Contractor grade, LEDtube, T8, 47-1/4 inch, 14.5 W, 3500 K, 1750 lm, 50000 hour(s), 120.00 lm/W, G13, Glass

Product data

General Information	
Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	1,750 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	120.00 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom) 70 %	
Operating and Electrical	
Line Frequency	50 to 60 Hz
Input Frequency	50 to 60 Hz
Power Consumption	14.5 W
Lamp Current (Max)	125 mA
Lamp Current (Min)	58 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B

Contractor-grade MainsFit (UL Type-B) T8

Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Limited
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T8
Net Weight (Piece)	0.419 lb
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes



Ambient temperature range	-4 °F to 113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	14.5T8/CNG/48-835/MF17/G 25/1
Full product name	14.5T8/CNG/48-835/MF17/G 25/1
Order code	577767
Material Nr. (12NC)	929003474504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677577766
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677577761

Dimensional drawing



Product	D1	D2	A1	A2	A3
14.5T8/CNG/48-835/MF17/G 25/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data




General uniform lighting - 14.5T8/CNG/48-835/MF17/G 25/1

Spectral Power Distribution Colour - 14.5T8/CNG/48-835/MF17/G 25/1


Contractor-grade MainsFit (UL Type-B) T8

Photometric data




Light Distribution Diagram - 14.5T8/CNG/48-835/MF17/G 25/1


Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 14.5T8/CNG/48-835/MF17/G 25/1



LEDtube 50K 7090 FailureRate-LED



Lumen Maintenance Diagram - 14.5T8/CNG/48-835/MF17/G 25/1

Contractor-grade MainsFit (UL Type-B) T8

Lifetime



LifetimeVsTc

