



Classic filament LEDbulbs

5A19/LED/950/FR/Glass/E26/DIM 1FB T20

Featuring a classic heritage design, Classic filament LEDbulbs combine the familiar shapes of classic incandescent bulbs with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light bulbs.

Product data

General Information			
Cap-Base	E26 [Single Contact Medium Screw]	Power Consumption	5 W
Nominal lifetime	15,000 hour(s)	Lamp Current (Nom)	55 mA
Switching Cycle	20,000	Wattage Equivalent	40 W
Lighting Technology	LED	Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	950 [CCT of 5000K]	Power Factor (Fraction)	0.7
Beam Angle (Nom)	320 degree(s)	Voltage (Nom)	120 V
Luminous Flux	450 lm	Controls and Dimming	
Color Designation	Daylight	Dimmable	Only with specific dimmers
Correlated Color Temperature (Nom)	5000 K	Mechanical and Housing	
Luminous Efficacy (rated) (Nom)	90.00 lm/W	Bulb Finish	Frosted
Color Consistency	<4	Bulb Material	Glass
Color rendering index (CRI)	90	Bulb Shape	A19
LLMF At End Of Nominal Lifetime (Nom)	70 %	UL Wet/ damp/ dry location	Wet location
Operating and Electrical		Net Weight (Piece)	0.033 kg
Line Frequency	60 Hz	Approval and Application	
Input Frequency	60 Hz	EU RoHS compliant	Yes

Classic filament LEDbulbs

T20 compliant	Yes
Ambient temperature range	-20 °C to 45 °C

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	5A19/LED/950/FR/Glass/E26/DIM 1FB T20
Full product name	5A19/LED/950/FR/Glass/E26/DIM 1FB T20


Order code	929003497504
Material Nr. (12NC)	929003497504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677578558
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677578553

Dimensional drawing




Product	D	C
5A19/LED/950/FR/Glass/E26/DIM 1FB T20	60 mm	105 mm


Photometric data



Spectral Power Distribution Colour - 5A19/LED/950/FR/Glass/E26/DIM 1FB T20




General uniform lighting - 5A19/LED/950/FR/Glass/E26/DIM 1FB T20



Light Distribution Diagram - 5A19/LED/950/FR/Glass/E26/DIM 1FB T20

Classic filament LEDbulbs

Lifetime



Life Expectancy Diagram

Lumen Maintenance Diagram - 5A19/LED/950/FR/Glass/E26/DIM 1FB T20

