

CorePro MainsFit (UL Type-B) T8

12T8/COR/48-840/MF18/G/DIM 25/1

CorePro, LEDtube, T8, 47-1/4 inch, 12 W, 4000 K, 1800 lm, 50000 hour(s)

CorePro, LEDtube, T8, 47-1/4 inch, 12 W, 4000 K, 1800 lm, 50000 hour(s), 150.00 lm/W, G13, Glass

Product data

General Information			
Cap-Base	G13	Input Frequency	50 to 60 Hz
Nominal lifetime	50,000 hour(s)	Power Consumption	12 W
Switching Cycle	50,000	Lamp Current (Max)	104 mA
Lighting Technology	LEDtube	Lamp Current (Min)	48 mA
		Wattage Equivalent	32 W
		Starting Time (Nom)	0.5 s
Light Technical		Warm-up time to 60% light	0.5 s
Color Code	840 [CCT of 4000K]	Power Factor (Fraction)	0.9
Beam Angle (Nom)	220 degree(s)	Voltage (Nom)	120-277 V
Luminous Flux	1,800 lm	UL Type	UL Type B
Color Designation	Cool White (CW)		
Correlated Color Temperature (Nom)	4000 K	Temperature	
Luminous Efficacy (rated) (Nom)	150.00 lm/W	T-Case Maximum (Nom)	158 °F
Color Consistency	6SCDM		
Color rendering index (CRI)	80	Controls and Dimming	
LLMF At End Of Nominal Lifetime (Nom)	70 %	Dimmable	Only with specific dimmers
Operating and Electrical			
Line Frequency	50 to 60 Hz	Mechanical and Housing	
		Bulb Finish	Frosted

CorePro MainsFit (UL Type-B) T8

Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T8
Net Weight (Piece)	0.441 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data



Order product name	12T8/COR/48-840/MF18/G/DIM 25/1
Full product name	12T8/COR/48-840/MF18/G/DIM 25/1
Order code	579383
Material Nr. (12NC)	929003524304
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677579388
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677579383

Dimensional drawing



Product	D1	D2	A1	A2	A3
12T8/COR/48-840/MF18/G/DIM 25/1	1-1/16 inch	1-1/8 inch	47-3/16 inch	47-1/2 inch	47-3/4 inch

Photometric data




General uniform lighting - 12T8/COR/48-840/MF18/G/DIM 25/1

Light Distribution Diagram - 12T8/COR/48-840/MF18/G/DIM 25/1


CorePro MainsFit (UL Type-B) T8

Photometric data




Spectral Power Distribution Colour - 12T8/COR/48-840/MF18/G/DIM 25/1


Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 12T8/COR/48-840/MF18/G/DIM 25/1



LEDtube 50K 7090 FailureRate-LED



Lumen Maintenance Diagram - 12T8/COR/48-840/MF18/G/DIM 25/1

CorePro MainsFit (UL Type-B) T8

Lifetime



LifetimeVsTc

