



Corepro InstantFit (UL Type-A) T8

28T8/COR/96-835/IF40/G/FA8 10/1

CorePro, LEDtube, T8, 94-1/2 inch, 28 W, 3500 K, 4000 lm, 50000 hour(s)

CorePro, LEDtube, T8, 94-1/2 inch, 28 W, 3500 K, 4000 lm, 50000 hour(s), 142.00 lm/W, FA8, Glass

Product data

General Information	
Cap-Base	FA8
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	240 degree(s)
Luminous Flux	4,000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	142.00 lm/W
Color Consistency	ANSI
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Line Frequency	35K to 150K Hz

Input Frequency	35K to 150K Hz
Power Consumption	28 W
Lamp Current (Max)	400 mA
Lamp Current (Min)	100 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	113 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

Corepro InstantFit (UL Type-A) T8

Bulb Material	Glass
Product Length	94-1/2 inch
Bulb Shape	T8
Net Weight (Piece)	0.882 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate
EU RoHS compliant	Yes
Ambient temperature range	-4 °F to 113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	28T8/COR/96-835/IF40/G/FA8 10/1
Full product name	28T8/COR/96-835/IF40/G/FA8 10/1
Order code	580282
Material Nr. (12NC)	929003556704
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677580285
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677580280

Dimensional drawing




Product	D1	D2	A1	A2	A3
28T8/COR/96-835/IF40/G/FA8 10/1	1-1/16 inch	1-1/8 inch	93-3/16 inch	93-9/16 inch	93-15/16 inch

Photometric data




Light Distribution Diagram - 28T8/COR/96-835/IF40/G/FA8 10/1



Spectral Power Distribution Colour - 28T8/COR/96-835/IF40/G/FA8 10/1



Corepro InstantFit (UL Type-A) T8

Photometric data





General Uniform Lighting - 28T8/COR/96-835/IF40/G/FA8 10/1

Lifetime



Lumen Maintenance Diagram - 28T8/COR/96-835/IF40/G/FA8 10/1

Life Expectancy Diagram




FailureRate

LifetimeVsTc

Corepro InstantFit (UL Type-A) T8

Lifetime



Lumen Maintenance Diagram - 28T8/COR/96-835/IF40/G/FA8 10/1

