



# Contractor-grade Plastic (Dimmable) A-Shape Lamps

8.8A19/CNG/840/FR/P/E26/D 12/1CT

Contractor grade, LEDbulb, A19, 60 W, E26, 4000 K, 800 lm, 15000 hour(s), Plastic

Contractor grade, LEDbulb, A19, 60 W, E26, 4000 K, 800 lm, 15000 hour(s), Plastic, 90 lm/W

## Product data

| General Information                |                    |
|------------------------------------|--------------------|
| Cap-Base                           | E26                |
| Nominal lifetime                   | 15,000 hour(s)     |
| Switching Cycle                    | 50,000             |
| Lighting Technology                | LEDbulb            |
| Light Technical                    |                    |
| Color Code                         | 840 [CCT of 4000K] |
| Beam Angle (Nom)                   | 180 degree(s)      |
| Luminous Flux                      | 800 lm             |
| Color Designation                  | Cool White (CW)    |
| Correlated Color Temperature (Nom) | 4000 K             |
| Luminous Efficacy (rated) (Nom)    | 90 lm/W            |
| Color Consistency                  | <6                 |
| Color rendering index (CRI)        | 80                 |


| LLMF At End Of Nominal Lifetime (Nom) | 70 %   |
|---------------------------------------|--------|
| Operating and Electrical              |        |
| Input Frequency                       | 60 Hz  |
| Power Consumption                     | 8.8 W  |
| Lamp Current (Nom)                    | 95 mA  |
| Wattage Equivalent                    | 60 W   |
| Starting Time (Nom)                   | 0.5 s  |
| Warm-up time to 60% light             | 0.5 s  |
| Power Factor (Fraction)               | 0.7    |
| Voltage (Nom)                         | 120 V  |
| Temperature                           |        |
| T-Case Maximum (Nom)                  | 194 °F |

Contractor-grade Plastic (Dimmable) A-Shape Lamps

|                            |                            |
|----------------------------|----------------------------|
| Controls and Dimming       |                            |
| Dimmable                   | Only with specific dimmers |
| Mechanical and Housing     |                            |
| Bulb Finish                | Frosted                    |
| Bulb Material              | Plastic                    |
| Bulb Shape                 | A19                        |
| UL Wet/ damp/ dry location | Damp location              |
| Net Weight (Piece)         | 0.057 lb                   |
| Approval and Application   |                            |
| EU RoHS compliant          | Yes                        |
| T20 compliant              | No                         |
| Ambient temperature range  | -4 to +113 °F              |



|                                     |                                  |
|-------------------------------------|----------------------------------|
| Application Conditions              |                                  |
| can it be used in closed luminaires | No                               |
| Wireless Technology                 | Not applicable                   |
| Product Data                        |                                  |
| Order product name                  | 8.8A19/CNG/840/FR/P/E26/D 12/1CT |
| Full product name                   | 8.8A19/CNG/840/FR/P/E26/D 12/1CT |
| Order code                          | 589671                           |
| Material Nr. (12NC)                 | 929003584964                     |
| Numerator - Quantity Per Pack       | 1                                |
| EAN/UPC - Product/Case              | 046677589677                     |
| Numerator - Packs per outer box     | 12                               |
| EAN/UPC - Case                      | 50046677589672                   |

Dimensional drawing



| Product                          | D          | C          |
|----------------------------------|------------|------------|
| 8.8A19/CNG/840/FR/P/E26/D 12/1CT | 2-3/8 inch | 4-1/8 inch |

Photometric data




General uniform lighting - 8.8A19/CNG/840/FR/P/E26/D 12/1CT

Light Distribution Diagram - 8.8A19/CNG/840/FR/P/E26/D 12/1CT


# Contractor-grade Plastic (Dimmable) A-Shape Lamps

## Photometric data




Spectral Power Distribution Colour - 8.8A19/CNG/840/FR/P/E26/D 12/1CT

## Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.8A19/CNG/840/FR/P/E26/D 12/1CT

