



Dipswitch LED bulb

8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT

LEDbulb, A19, 60 W, E26, Selectable, 2700 K, 3000 K, 3500 K, 4000 K, 5000 K, 800 lm, 15000 hour(s), Plastic

LEDbulb, A19, 60 W, E26, Selectable, 2700 K, 3000 K, 3500 K, 4000 K, 5000 K, 800 lm, 15000 hour(s), Plastic, 100 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	2700/3000/3500/4000/5000
Beam Angle (Nom)	220 degree(s)
Luminous Flux	800 lm
Color Designation	2700/3000/3500/4000/5000
Correlated Color Temperature (Nom)	Selectable 2700 3000 3500 4000 5000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	8 W
Lamp Current (Nom)	90 mA

Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	194 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Overall length	4-7/16 inch
Overall width	2-3/8 inch
Overall height	4-7/16 inch
Dimensions (Height x Width x Depth)	112 x 60 x 112 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location

Dipswitch LED bulb

Net Weight (Piece)	0.077 lb
--------------------	----------

Approval and Application


EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	EyeComfort
Ambient temperature range	-4 to +113 °F

Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable



Product Data	
Order product name	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT
Full product name	8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT
Order code	586875
Material Nr. (12NC)	929003620333
Numerator - Quantity Per Pack	4
EAN/UPC - Product/Case	046677586874
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677586879

Dimensional drawing



Product	D	C
8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT	2-3/8 inch	4-7/16 inch

Photometric data




General uniform lighting - 8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT

Spectral Power Distribution Colour - 8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT


Dipswitch LED bulb

Photometric data




Light Distribution Diagram - 8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8A19/DipS/5CCT/FR/P/E26/DIM/T20 3/4CT

