



Contractor-grade Plastic (Dimmable) A-Shape Lamps

11A19/CNG/840/FR/P/E26/D 12/1CT

Contractor grade, LEDbulb, A19, 75 W, E26, 4000 K, 1100 lm, 15000 hour(s), Plastic

Contractor grade, LEDbulb, A19, 75 W, E26, 4000 K, 1100 lm, 15000 hour(s), Plastic, 100 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	180 degree(s)
Luminous Flux	1,100 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	100 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	11 W
Lamp Current (Nom)	115 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	221 °F

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.071 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-4 to +113 °F



Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	11A19/CNG/840/FR/P/E26/D 12/1CT
Full product name	11A19/CNG/840/FR/P/E26/D 12/1CT
Order code	589705
Material Nr. (12NC)	929003751964
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677589707
Numerator - Packs per outer box	12
EAN/UPC - Case	50046677589702

Dimensional drawing



Product	D	C
11A19/CNG/840/FR/P/E26/D 12/1CT	2-3/8 inch	4-3/16 inch

Photometric data




Spectral Power Distribution Colour - 11A19/CNG/840/FR/P/E26/D 12/1CT

General uniform lighting - 11A19/CNG/840/FR/P/E26/D 12/1CT

Contractor-grade Plastic (Dimmable) A-Shape Lamps

Photometric data




Light Distribution Diagram - 11A19/CNG/840/FR/P/E26/D 12/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 11A19/CNG/840/FR/P/E26/D 12/1CT

