



LED PAR30 S/L

8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB

LEDspot, PAR30L, 75 W, E26, 4000 K, 900 lm, 25000 hour(s), Plastic

LEDspot, PAR30L, 75 W, E26, 4000 K, 900 lm, 25000 hour(s), Plastic, 105 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	25,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot

Light Technical	
Color Code	940 [CCT of 4000K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	900 lm
Luminous Intensity (Nom)	1,600 cd
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	105 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	8.5 W
Lamp Current (Nom)	105 mA

Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	185 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30L
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.165 lb


Approval and Application	
Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes

LED PAR30 S/L

T20 compliant	Yes
Ambient temperature range	-40 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB



Full product name	8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB
Order code	587410
Material Nr. (12NC)	929003753504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677587413
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677587418

Dimensional drawing



Product	D	C
8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB	3-3/4 inch	4-5/8 inch

Photometric data




Accent Lighting Spots - 8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB

Light Distribution Diagram - 8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB


LED PAR30 S/L

Photometric data




Spectral Power Distribution Colour -
8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 8.5PAR30L/COR/940/F40/D/P/ULW/T20 6/1FB

