



CorePro LED PLC 2P

LED PLC 6.9W 830 2P G24d-2

LED, PL-C, EM/Mains, 4-15/16 inch, 220-240 V, 6.9 W, 18W PL-C, 3000 K, 700 lm, 30000 hour(s)

LED, PL-C, EM/Mains, 4-15/16 inch, 220-240 V, 6.9 W, LED alternative to 18W PL-C, 3000 K, 700 lm, 30000 hour(s), 101 lm/W, G24D-2 Rotatable end-cap, Beam angle 120 degree(s), Plastic, RG1

Product data

General Information	
Cap-Base	G24D-2 Rotatable end-cap
Nominal lifetime	30,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Warranty period	3 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	700 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	101 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471 RG1	

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6.9 W
Lamp Current (Nom)	38 mA
Wattage Equivalent	18 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18W PL-C
Ballast Compatibility	EM/Mains
Temperature	
T-Case Maximum (Nom)	167 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

CorePro LED PLC 2P

Bulb Material	Plastic
Product Length	4-15/16 inch
Bulb Shape	PL-C
Net Weight (Piece)	0.165 lb


Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keurmerk certificate
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-4 to +95 °F

Application Conditions


Wireless Technology	Not applicable
---------------------	----------------

Dimensional drawing



D	D1	A1	A2	A3
34 mm	34mm	106mm	125mm	148mm

Photometric data




Light Distribution Diagram - LED PLC 6.9W 830 2P G24d-2

Product Data


Order product name	LED PLC 6.9W 830 2P G24d-2
Full product name	LED PLC 6.9W 830 2P G24d-2
Full product code	872016929642800
Order code	929003757208
Material Nr. (12NC)	929003757208
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169296428
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169296435

Product	D1	D	A1	A2	A3
LED PLC 6.9W 830 2P	1-3/8 inch	1-3/8 inch	4-3/16 inch	4-15/16 inch	5-7/8 inch
G24d-2					





Spectral Power Distribution Colour - LED PLC 6.9W 830 2P G24d-2

Photometric data




General uniform lighting - LED PLC 6.9W 830 2P G24d-2


Lifetime



Life Expectancy Diagram



LifetimeVsTc




Lumen Maintenance Diagram - LED PLC 6.9W 830 2P G24d-2

FailureRate

CorePro LED PLC 2P

Lifetime



Lumen Maintenance Diagram - LED PLC 6.9W 830 2P G24d-2

