




MASTER UltraEfficient LED bulb

5A19/UE/950/CL/G/E26/D T20 3/4CT

MASTER, LEDbulb, A19, 60 W, E26, 5000 K, 850 lm, 50000 hour(s), Glass

MASTER, LEDbulb, A19, 60 W, E26, 5000 K, 850 lm, 50000 hour(s), Glass, 170 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	50,000 hour(s)
Switching Cycle	100,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	950 [CCT of 5000K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	850 lm
Color Designation	Daylight
Correlated Color Temperature (Nom)	5000 K
Luminous Efficacy (rated) (Nom)	170 lm/W
Color Consistency	<4
Color rendering index (CRI)	90
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	5 W
Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.7
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Glass
Overall length	4-3/16 inch

MASTER UltraEfficient LED bulb

Overall width	2-3/8 inch
Overall height	4-3/16 inch
Dimensions (Height x Width x Depth)	105 x 60 x 105 mm
Bulb Shape	A19
UL Wet/ damp/ dry location	Wet location
Net Weight (Piece)	0.079 lb
Approval and Application	
EU RoHS compliant	Yes
EyeComfort	Yes
T20 compliant	Yes
LED Innovations	UltraEfficient
Ambient temperature range	-4 to +104 °F
Application Conditions	
can it be used in closed luminaires	No


Wireless Technology	Not applicable
Product Data	
Order product name	5A19/UE/950/CL/G/E26/D T20 3/4CT
Full product name	5A19/UE/950/CL/G/E26/D T20 3/4CT
Order code	592428
Material Nr. (12NC)	929003765403
Numerator - Quantity Per Pack	4
EAN/UPC - Product/Case	046677592424
Numerator - Packs per outer box	3
EAN/UPC - Case	50046677592429

Dimensional drawing




Product	D	C
5A19/UE/950/CL/G/E26/D T20 3/4CT	2-3/8 inch	4-3/16 inch

Photometric data




Spectral Power Distribution Colour - 5A19/UE/950/CL/G/E26/D T20 3/4CT



Light Distribution Diagram - 5A19/UE/950/CL/G/E26/D T20 3/4CT

MASTER UltraEfficient LED bulb


Photometric data




General uniform lighting - 5A19/UE/950/CL/G/E26/D T20 3/4CT

General uniform lighting - 5A19/UE/950/CL/G/E26/D T20 3/4CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 5A19/UE/950/CL/G/E26/D T20 3/4CT

