



CorePro LEDtube InstantFit HF T5



CorePro LEDtube HF 600mm HE 7.1W 840T5

CorePro, LEDtube, T5, HF, 600 mm, 7.1 W, 14W TL5 HE, 4000 K, 1050 lm, CRI 80, 50000 h

CorePro LEDtube InstantFit HF T5 is the quick and easy way to replace T5 fluorescent tubes with a fast payback time. Designed with industry leading ballast compatibility, the product is ideal for your everyday lighting jobs. With simply plug-and-play installation, it improves energy efficiency immediately and lasts for longer than conventional T5.

Product data

General Information		Colour rendering index (CRI)	
Cap base	G5		80
Nominal lifetime	50,000 h	LLMF at end of nominal lifetime (nom.)	70 %
Switching Cycle	50,000	Photobiological safety according to EN 62471	RG0
Lighting Technology	LEDtube	Operating and Electrical	
Flux measurement reference	Sphere	Input frequency	30 K to 100 K Hz
Warranty period	3 years	Power Consumption	7.1 W
Light Technical		Lamp current (max.)	350 mA
Colour Code	840 [CCT of 4000K]	Lamp current (min.)	150 mA
Beam angle (nom.)	200 degree(s)	Starting time (nom.)	0.5 s
Luminous Flux	1,050 lm	Warm-up time to 60% light	0.5 s
Colour designation	Cool White (CW)	Power Factor (Fraction)	0.9
Correlated Colour Temperature (Nom)	4000 K	Voltage (nom.)	40-70 V
Luminous efficacy (rated) (nom.)	147 lm/W	LED alternative to fluorescent lamp power	14W TL5 HE
Colour consistency	<6	Inrush current at mains	-
		Max. lamp no. on MCB B type 10A — Mains	-

CorePro LEDtube InstantFit HF T5

Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – Mains	-
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	HF

Temperature

T-Case maximum (nom.)	45 °C
-----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Product length	600 mm
Bulb shape	T5
Net Weight (Piece)	0.085 kg

Approval and Application

Energy Efficiency Class	D
-------------------------	---

Energy-saving product	Yes
Approval marks	RoHS compliance KEMA Keur certificate
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	1880102
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-20 to +45 °C


Application Conditions

Wireless Technology	Not applicable
---------------------	----------------

Product Data

Order product name	CorePro LEDtube HF 600mm HE 7.1W 840T5
Full product name	CorePro LEDtube HF 600mm HE 7.1W 840T5
Full EOC	872016929542100
Order code	929003774202
Material no. (12 NC)	929003774202
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169295421
Numerator – packs per outer box	10
EAN/UPC – Case	8720169295438



Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 600mm HE 7.1W 840T5	15.5 mm	16/19 mm	549 mm	556 mm	563 mm


CorePro LEDtube InstantFit HF T5

Photometric data



General uniform lighting - CorePro LEDtube HF 600mm HE 7.1W 840T5

Spectral Power Distribution Colour - CorePro LEDtube HF 600mm HE 7.1W 840T5



Light Distribution Diagram - CorePro LEDtube HF 600mm HE 7.1W 840T5

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDtube HF 600mm HE 7.1W 840T5

CorePro LEDtube InstantFit HF T5

Lifetime



FailureRate

LifetimeVsTc



Lumen Maintenance Diagram - CorePro LEDtube HF 600mm HE 7.1W 840T5

