



CorePro LED tube InstantFit HF T5

CorePro LEDtube HF 1200mm HE 17.1W 830T5

CorePro, LEDtube, T5, HF, 47-1/4 inch, 17.1 W, 28W TL5 HE, 3000 K, 2300 lm, CRI 80, 50000 hour(s)

CorePro, LEDtube, T5, HF, 47-1/4 inch, 17.1 W, LED alternative to 28W TL5 HE, 3000 K, 2300 lm, CRI 80, 50000 hour(s), 134 lm/W, EEL E, G5, Beam angle 200 degree(s), Glass, 1200 mm, RG0, SDCM 6, PF 0.9, IP20

Product data

General Information	
Cap-Base	G5
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	200 degree(s)
Luminous Flux	2,300 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	134 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Input Frequency	30K to 100K Hz
Power Consumption	17.1 W
Lamp Current (Max)	350 mA
Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	70-120 V
LED alternative to fluorescent lamp power	28W TL5 HE
Inrush current at mains	-
Max. lamp no. on MCB B type 10A - Mains	-
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-

CorePro LED tube InstantFit HF T5

Max. lamp no. on MCB B type 16A – Mains	-
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-
Ballast Compatibility	HF
Temperature	
T-Case Maximum (Nom)	113 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T5
Net Weight (Piece)	0.353 lb
Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	RoHS compliance KEMA Keur certificate

Energy Consumption kWh/1000 h	18 kWh
EPREL Registration Number	1880104
CE mark	Yes
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
Wireless Technology	Not applicable
Product Data	
Order product name	CorePro LEDtube HF 1200mm HE 17.1W 830T5
Full product name	CorePro LEDtube HF 1200mm HE 17.1W 830T5
Full product code	872016929546900
Order code	929003774402
Material Nr. (12NC)	929003774402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169295469
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169295476


Dimensional drawing




Product	D1	D2	A1	A2	A3
CorePro LEDtube HF 1200mm HE 17.1W 830T5	5/8 inch	0 inch	45-1/4 inch	45-9/16 inch	45-13/16 inch

CorePro LED tube InstantFit HF T5


Photometric data



Spectral Power Distribution Colour - CorePro LEDtube HF 1200mm HE 17.1W 830T5




General uniform lighting - CorePro LEDtube HF 1200mm HE 17.1W 830T5




Light Distribution Diagram - CorePro LEDtube HF 1200mm HE 17.1W 830T5

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - CorePro LEDtube HF 1200mm HE 17.1W 830T5

CorePro LED tube InstantFit HF T5

Lifetime



FailureRate



LifetimeVsTc

Lumen Maintenance Diagram - CorePro LEDtube HF 1200mm HE 17.1W 830T5

