



FlexFit (Hybrid UL Type A + B) T8

10.5T8/COR/36-5CCT/FF15/G/DIM 25/1

CorePro, LEDtube, T8, 35-7/16 inch, 10.5, 3000 K, 3500 K, 4000 K, 5000 K, 6500 K, 1400 lm, 1400 lm, 1500 lm, 1500 lm, 1500 lm, 50000 hour(s)

CorePro, LEDtube, T8, 35-7/16 inch, 10.5, 3000 K, 3500 K, 4000 K, 5000 K, 6500 K, 1400 lm, 1400 lm, 1500 lm, 1500 lm, 1500 lm, 50000 hour(s), 136 lm/W, G13, Glass

Product data

General Information	
Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	3000K/3500K/4000K/5000K/6500K
Beam Angle (Nom)	220 degree(s)
Luminous Flux	1,400 1,400 1,500 1,500 1,500 lm
Color Designation	3000K/3500K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	3000 3500 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10.5
Lamp Current (Max)	108 mA
Lamp Current (Min)	48 mA
Wattage Equivalent	25 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type A+B
Temperature	
T-Case Maximum (Nom)	131 °F

FlexFit (Hybrid UL Type A + B) T8

Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	35-7/16 inch
Bulb Shape	T8
Net Weight (Piece)	0.392 lb
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F


Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	10.5T8/COR/36-5CCT/FF15/G/DIM 25/1
Full product name	10.5T8/COR/36-5CCT/FF15/G/DIM 25/1
Order code	588632
Material Nr. (12NC)	929003794604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588632
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677588637

Dimensional drawing




Product	D1	D2	A1	A2	A3
10.5T8/COR/36-5CCT/ FF15/G/DIM 25/1	1-1/16 inch	1-1/8 inch	35-3/16 inch	35-1/2 inch	35-3/4 inch

Photometric data




Spectral Power Distribution Colour - 10.5T8/COR/36-5CCT/FF15/G/DIM 25/1



General uniform lighting - 10.5T8/COR/36-5CCT/FF15/G/DIM 25/1


FlexFit (Hybrid UL Type A + B) T8

Photometric data




Light Distribution Diagram - 10.5T8/COR/36-5CCT/FF15/G/DIM 25/1


Lifetime




Lumen Maintenance Diagram - 10.5T8/COR/36-5CCT/FF15/G/DIM 25/1



Life Expectancy Diagram




FailureRate



Lumen Maintenance Diagram - 10.5T8/COR/36-5CCT/FF15/G/DIM 25/1

FlexFit (Hybrid UL Type A + B) T8

Lifetime



LifetimeVsTc

