



Contractor-grade Plastic (Non- Dimmable) A-Shape Lamps

10A19/CNG/830/FR/P/E26/ND 4/1CT

Contractor grade, LEDbulb, A19, 75 W, E26, 3000 K, 1000 lm, 15000 hour(s), Plastic

Contractor grade, LEDbulb, A19, 75 W, E26, 3000 K, 1000 lm, 15000 hour(s), Plastic, 100 lm/W

Product data

General Information	
Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb
Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,000 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	100 lm/W


Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz
Power Consumption	10 W
Lamp Current (Nom)	185 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5

Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps

Voltage (Nom)	120 V
Temperature	
T-Case Maximum (Nom)	194 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.066 lb
Approval and Application	
EU RoHS compliant	Yes
T20 compliant	No


Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	10A19/CNG/830/FR/P/E26/ND 4/1CT
Full product name	10A19/CNG/830/FR/P/E26/ND 4/1CT
Order code	588905
Material Nr. (12NC)	929003798364
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588908
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677588903

Dimensional drawing




Product	D	C
10A19/CNG/830/FR/P/E26/ND 4/1CT	2-3/8 inch	4-3/16 inch

Photometric data




Light Distribution Diagram - 10A19/CNG/830/FR/P/E26/ND 4/1CT



Spectral Power Distribution Colour - 10A19/CNG/830/FR/P/E26/ND 4/1CT

Contractor-grade Plastic (Non-Dimmable) A-Shape Lamps


Photometric data




General uniform lighting - 10A19/CNG/830/FR/P/E26/ND 4/1CT

General uniform lighting - 10A19/CNG/830/FR/P/E26/ND 4/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 10A19/CNG/830/FR/P/E26/ND 4/1CT

