



MainsFit (UL Type-B) T5

9T5HE/COR/22-5CCT/MF12/G 25/1

CorePro, LEDtube, T5, 23-5/8 inch, 9 W, 3000 K, 3500 K, 4000 K, 5000 K, 6500 K, 1200 lm, 50000 hour(s)

CorePro, LEDtube, T5, 23-5/8 inch, 9 W, 3000 K, 3500 K, 4000 K, 5000 K, 6500 K, 1200 lm, 50000 hour(s), 133 lm/W, G5, Glass, RG0

Product data

General Information	
Cap-Base	G5
Nominal lifetime	50,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube
Light Technical	
Color Code	3000K/3500K/4000K/5000K/6500K
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,200 lm
Color Designation	3000K/3500K/4000K/5000K/6500K
Correlated Color Temperature (Nom)	3000 3500 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	9 W
Lamp Current (Nom)	80 mA
Wattage Equivalent	14 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted

MainsFit (UL Type-B) T5

Bulb Material	Glass
Product Length	23-5/8 inch
Bulb Shape	T5
Net Weight (Piece)	0.198 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate KEMA Keur certificate
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Wireless Technology	Not applicable
---------------------	----------------

Product Data


Order product name	9T5HE/COR/22-5CCT/MF12/G 25/1
Full product name	9T5HE/COR/22-5CCT/MF12/G 25/1
Order code	592774
Material Nr. (12NC)	929004235104
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677592776
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677592771

Dimensional drawing




Product	D1	D2	A1	A2	A3
9T5HE/COR/22-5CCT/ MF12/G 25/1	5/8 inch	15/16 inch	21-9/16 inch	21-7/8 inch	22-3/16 inch

Photometric data




Light Distribution Diagram - 9T5HE/COR/22-5CCT/MF12/G 25/1



General uniform lighting - 9T5HE/COR/22-5CCT/MF12/G 25/1


MainsFit (UL Type-B) T5

Photometric data




Spectral Power Distribution Colour - 9T5HE/COR/22-5CCT/MF12/G 25/1


Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 9T5HE/COR/22-5CCT/MF12/G 25/1




LEDtube 50K 7090 FailureRate-LED



Lumen Maintenance Diagram - 9T5HE/COR/22-5CCT/MF12/G 25/1

MainsFit (UL Type-B) T5

Lifetime



LifetimeVsTc

