



InstantFit (UL Type A) Circline

22CIR/CNG/16-4CCT/IF26/P/G10q 6/1

CorePro, LED, C-T9, 13-7/16 inch, 22 W, 3000 K, 4000 K, 5000 K, 6500 K, 2600 lm, 36000 hour(s)

CorePro, LED, C-T9, 13-7/16 inch, 22 W, 3000 K, 4000 K, 5000 K, 6500 K, 2600 lm, 36000 hour(s), 118 lm/W, G10q, Plastic

Product data

General Information	
Cap-Base	G10q
Nominal lifetime	36,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	3000/4000/5000/6500
Beam Angle (Nom)	120 degree(s)
Luminous Flux	2,600 lm
Color Designation	3000/4000/5000/6500
Correlated Color Temperature (Nom)	3000 4000 5000 6500 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
All-in Type	All-in, Multi Color Temperature

Operating and Electrical	
Input Frequency	50 to 80K Hz
Power Consumption	22 W
Lamp Current (Max)	1,060 mA
Lamp Current (Min)	410 mA
Wattage Equivalent	40 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.2
Voltage (Nom)	120-277 V
UL Type	UL Type A
Temperature	
T-Case Maximum (Nom)	131 °F
Controls and Dimming	
Dimmable	No

InstantFit (UL Type A) Circline

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	13-7/16 inch
Bulb Shape	C-T9
Net Weight (Piece)	0.661 lb


Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F

Application Conditions	
can it be used in closed luminaires	Yes

Wireless Technology	Not applicable
---------------------	----------------


Product Data	
Order product name	22CIR/CNG/16-4CCT/IF26/P/G10q 6/1
Full product name	22CIR/CNG/16-4CCT/IF26/P/G10q 6/1
Order code	605010
Material Nr. (12NC)	929004236004
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677605018
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677605013

Dimensional drawing




Product	D1	D	A1	A2	A3
22CIR/CNG/16-4CCT/IF26/P/G10q 6/1		1-3/16 inch	1-3/16 inch	13-7/16 inch	15-3/4 inch

Photometric data




Spectral Power Distribution Colour - 22CIR/CNG/16-4CCT/IF26/P/G10q 6/1





Light Distribution Diagram - 22CIR/CNG/16-4CCT/IF26/P/G10q 6/1

Photometric data




General uniform lighting - 22CIR/CNG/16-4CCT/IF26/P/G10q 6/1

Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 22CIR/CNG/16-4CCT/IF26/P/G10q 6/1


Life Expectancy Diagram



Lumen Maintenance Diagram - 22CIR/CNG/16-4CCT/IF26/P/G10q 6/1

InstantFit (UL Type A) Circline

Lifetime



Life Expectancy Diagram

