



MasterClass MainsFit (UL Type-B) T8

11.5T8/MAS/48-835/MF21/G/DIM UE 25/1

MasterClass, LEDtube, T8, 47-1/4 inch, 11.5 W, 3500 K, 2100 lm, 50000 hour(s)

MasterClass, LEDtube, T8, 47-1/4 inch, 11.5 W, 3500 K, 2100 lm, 50000 hour(s), 182 lm/W, G13, Glass, 0 %

Product data

General Information	
Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	835 [CCT of 3500K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	2,100 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3500 K
Luminous Efficacy (rated) (Nom)	182 lm/W
Color Consistency	6SCDM
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz

Power Consumption	11.5 W
Lamp Current (Max)	130 mA
Lamp Current (Min)	48 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B
Temperature	
T-Case Maximum (Nom)	122 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass

MasterClass MainsFit (UL Type-B) T8

Product Length	47-1/4 inch
Bulb Shape	T8
Net Weight (Piece)	0.441 lb

Approval and Application

Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Post-consumer recycled plastic material ratio	0 %

Application Conditions


can it be used in closed luminaires	Yes
Wireless Technology	Not applicable

Sustainability Data	
Product non-virgin material ratio	0 %

Product Data


Order product name	11.5T8/MAS/48-835/MF21/G/DIM UE 25/1
Full product name	11.5T8/MAS/48-835/MF21/G/DIM UE 25/1
Order code	607457
Material Nr. (12NC)	929004282804
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677607456
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677607451

Dimensional drawing




Product	D1	D2	A1	A2	A3
11.5T8/MAS/48-835/MF21/G/DIM UE 25/1	1-1/16 inch	1-1/8 inch	47-1/4 inch	47-1/2 inch	47-13/16 inch

Photometric data




Spectral Power Distribution Colour - 11.5T8/MAS/48-835/MF21/G/DIM UE 25/1



Light Distribution Diagram - 11.5T8/MAS/48-835/MF21/G/DIM UE 25/1



MasterClass MainsFit (UL Type-B) T8

Photometric data




General uniform lighting - 11.5T8/MAS/48-835/MF21/G/DIM UE 25/1

Lifetime




Life Expectancy Diagram



Lumen Maintenance Diagram - 11.5T8/MAS/48-835/MF21/G/DIM UE 25/1


FailureRate



LifetimeVsTc

MasterClass MainsFit (UL Type-B) T8

Lifetime



Lumen Maintenance Diagram - 11.5T8/MAS/48-835/MF21/G/DIM UE 25/1

