



Contractor-grade MainsFit (UL Type-B) T8

15.3T8/CNG/48-840/MX21/G 25/1

Contractor grade, LEDtube, T8, 47-1/4 inch, 15.3 W, 4000 K, 2100 lm, 50000 hour(s)

Contractor grade, LEDtube, T8, 47-1/4 inch, 15.3 W, 4000 K, 2100 lm, 50000 hour(s), 137 lm/W, G13, Glass, 0 %

Product data

General Information	
Cap-Base	G13
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDtube
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	220 degree(s)
Luminous Flux	2,100 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	137 lm/W
Color Consistency	<6
Color rendering index (CRI)	80


LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	15.3 W
Lamp Current (Max)	168 mA
Lamp Current (Min)	63 mA
Wattage Equivalent	32 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
UL Type	UL Type B

Contractor-grade MainsFit (UL Type-B) T8

Temperature	
T-Case Maximum (Nom)	140 °F
Controls and Dimming	
Dimmable	Limited
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	47-1/4 inch
Bulb Shape	T8
Net Weight (Piece)	0.441 lb
Approval and Application	
Energy Saving Product	Yes
Approval Marks	RoHS compliance UL certificate DLC compliance
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Post-consumer recycled plastic material ratio	0 %


Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Sustainability Data	
Product non-virgin material ratio	0 %
Product Data	
Order product name	15.3T8/CNG/48-840/MX21/G 25/1
Full product name	15.3T8/CNG/48-840/MX21/G 25/1
Order code	610329
Material Nr. (12NC)	929004351604
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677610326
Numerator - Packs per outer box	25
EAN/UPC - Case	50046677610321

Dimensional drawing




Product
15.3T8/CNG/48-840/MX21/G 25/1

Photometric data




Light Distribution Diagram - 15.3T8/CNG/48-840/MX21/G 25/1



Spectral Power Distribution Colour - 15.3T8/CNG/48-840/MX21/G 25/1

Contractor-grade MainsFit (UL Type-B) T8


Photometric data




General Uniform Lighting - 15.3T8/CNG/48-840/MX21/G 25/1

General uniform lighting - 15.3T8/CNG/48-840/MX21/G 25/1


Lifetime




Lumen Maintenance Diagram - 15.3T8/CNG/48-840/MX21/G 25/1



LifetimeVsTc




Life Expectancy Diagram



FailureRate

Contractor-grade MainsFit (UL Type-B) T8

Lifetime



Lumen Maintenance Diagram - 15.3T8/CNG/48-840/MX21/G 25/1

