



PL-L

10PL-L/COR/24-5CCT/MF11/G/4P 10/1

CorePro, LED, PL-L, 12-1/4 inch, 10 W, 2700 K, 3000 K, 3500 K, 4000 K, 5000 K, 1100 lm, 1100 lm, 1100 lm, 1150 lm, 1150 lm, 50000 hour(s)

CorePro, LED, PL-L, 12-1/4 inch, 10 W, 2700 K, 3000 K, 3500 K, 4000 K, 5000 K, 1100 lm, 1100 lm, 1100 lm, 1150 lm, 1150 lm, 50000 hour(s), 115 lm/W, 2G11, Glass

Product data


General Information	
Cap-Base	2G11
Nominal lifetime	50,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LED
Light Technical	
Color Code	2700/3000/3500/4000/5000
Beam Angle (Nom)	140 degree(s)
Luminous Flux	1,100 1,100 1,100 1,150 1,150 lm
Color Designation	2700/3000/3500/4000/5000
Correlated Color Temperature (Nom)	2700 3000 3500 4000 5000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	10 W

Lamp Current (Max)	110 mA
Lamp Current (Min)	50 mA
Wattage Equivalent	24 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120-277 V
Temperature	
T-Case Maximum (Nom)	167 °F
Controls and Dimming	
Dimmable	Only with specific dimmers
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Product Length	12-1/4 inch
Bulb Shape	PL-L

Net Weight (Piece)	0.234 lb
Approval and Application	
EU RoHS compliant	Yes
Ambient temperature range	-4 to +113 °F
Application Conditions	
can it be used in closed luminaires	Yes
Wireless Technology	Not applicable
Product Data	
Order product name	10PL-L/COR/24-5CCT/MF11/G/4P 10/1


Full product name	10PL-L/COR/24-5CCT/MF11/G/4P 10/1
Order code	607135
Material Nr. (12NC)	929004602504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677607135
Numerator - Packs per outer box	10
EAN/UPC - Case	50046677607130

Dimensional drawing




Product	D1	D	A1	A2	A3
10PL-L/COR/24-5CCT/ MF11/G/4P 10/1	7/8 inch	1-5/8 inch	9-1/2 inch	12-1/4 inch	12-5/8 inch

Photometric data




Spectral Power Distribution Colour - 10PL-L/COR/24-5CCT/MF11/G/4P 10/1




General uniform lighting - 10PL-L/COR/24-5CCT/MF11/G/4P 10/1

Photometric data




Light Distribution Diagram - 10PL-L/COR/24-5CCT/MF11/G/4P 10/1


Lifetime




Lumen Maintenance Diagram - 10PL-L/COR/24-5CCT/MF11/G/4P 10/1



Life Expectancy Diagram




Lumen Maintenance Diagram - 10PL-L/COR/24-5CCT/MF11/G/4P 10/1



LEDtube 50K 7595 LifetimeVsTc-LED

Lifetime



LEDtube 50K 7595 FailureRate-LED

