



Energy Saver GU24

23 W (100 W) GU24 base Soft White Spiral

Looking for an energy saver that doesn't look like one? The Philips Energy Saver family provides energy-efficient lighting options that don't just deliver similar light as your standard incandescent light bulb, they also have the same classic shape. Try Philips Energy Savers and see how they truly offer advanced lighting to meet your needs.

Product data


General Information	
Cap-Base	GU24
Nominal lifetime	10,000 hour(s)
Switching Cycle	5,000
Rated Lifetime (Hours)	10,000 hour(s)
Lighting Technology	Compact Fluorescent Integrated
Light Technical	
Color Code	827 [CCT of 2700K]
Luminous Flux	1,600 lm
Color Designation	Warm White (WW)
Chromaticity Coordinate X (Nom)	459
Chromaticity Coordinate Y (Nom)	412
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	67 lm/W
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	50 %
Operating and Electrical	
Line Frequency	50 or 60 Hz
Input Frequency	50 or 60 Hz
Power Consumption	23.0 W

Lamp Current (Nom)	360 mA
Power Factor (Fraction)	0.55
Voltage (Nom)	110-127 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Shape	EL/mdTQS
Net Weight (Piece)	0.086 kg
Approval and Application	
Mercury (Hg) Content (Max)	2.5 mg
Energy Consumption kWh/1000 h	23 kWh
Product Data	
Order product name	23 W (100 W) GU24 base Soft White Spiral
Full product name	23 W (100 W) GU24 base Soft White Spiral
Order code	929689791501
Material Nr. (12NC)	929689791501
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677454210

Energy Saver GU24

Numerator - Packs per outer box	6
EAN/UPC - Case	50046677454215

Dimensional drawing



Product	D (max)	C (max)	F (max)
23 W (100 W) GU24 base Soft White Spiral	61.5 mm	110.0 mm	50.5 mm

