

Project: \_\_\_\_\_

Location: \_\_\_\_\_

Cat.No: \_\_\_\_\_

Type: \_\_\_\_\_


Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_

Notes: \_\_\_\_\_

### Ordering Guide

Example: 536 ABS A D 50H E B N

Product Code	536	Stockholm
<b>Finish</b>	ABS ACP ARD ASI BLK BRN BRZ FGN GRA IRN IRN RBZ SRT VBZ VCP VGN VTC WBZ WHT	Antique Brass Antique Copper Antique Red Antique Silver Black Brown Bronze Forest Green Granite Ironstone Ironstone Rustic Bronze Shadow Rust Verde Bronze Verde Copper Verde Vintage Copper Weathered Bronze White
<b>Panel/Globe</b>	A	Clear Acrylic
<b>Socket</b>	D G L	Medium Mogul LED
<b>Wattage/Source</b>	50H 70H 35S 50S 70S 100S 100I LED	50W MH 70W MH 35W HPS 50W HPS 70W HPS 100W HPS 100W INC. LED
<b>Voltage</b>	E F G H	120V 208V 240V 277V
<b>Distribution</b>	B C N	6" Type V Distrib. 6" Type III Distrib. None
<b>Photoeye</b>	N	None



# 536 Stockholm

## Side arm mount

### Specifications

---

**CONSTRUCTION:**

Cast aluminum finial. Spun aluminum cap. Spun aluminum roof. Fluted cast aluminum top ring. 4 Cast aluminum legs. Cast aluminum refractor support. Cast aluminum cap. Cast aluminum "S" fluted bracket arm and wall plate.

**FINISH:**

Resilient TGIC thermoset polyester powdercoat paint is electrostatically applied to every fixture. Specially formulated for Philips Outdoor Lighting, it provides UV protection, and the highest temperature rating in the industry. In addition to the standard color choices shown, a spectrum of custom colors is available.

**PANELS/LENS/GLOBE:**

See lenses for available options.

**LAMPING:**

Lamp is not included.

**ELECTRICAL ASSEMBLY:**

Lantern will be prewired and tested. All electrical components are ETL listed.

**BALLAST:**

Ballast and component parts mounted inside two-piece cast aluminum moisture proof ballast compartment. (Customer must specify wattage and voltage.)

**MOUNTING:**

See template for dimensions & mounting instructions.

**WARRANTY:**

Three-year limited warranty.

**CERTIFICATIONS:**

ETL Listed to U.S. safety standards for wet locations. cETL Listed to Canadian safety standards for wet locations.

**Height:**

41 1/2"

**Width:**

17 3/4"

**Projection:**

21 1/2"

**Top to Outlet:**

29"

**Max. Weight:**

28 lbs.

