


PHILIPS

Diamond Cut
A Class downlight

DL264



A

CE

Ta 25°C

Max. 40°C
Min. -20°C

220-240
V(AC)

50/60
Hz


01

18

30

55

Model	Product Description	Power(W)	CRI(Ra)	CCT(K)	Total Lumen(lm)	Energy efficiency class of light source	Dimension AxB,C(mm)	Cut-Out D(mm)	Weight (kg)
9290032588	DIAMOND CUT A Class DL264 RD075 30K WH	2	80	3000	360	A	φ95*49.5,48	φ68-80	0.083
9290032481	DIAMOND CUT A Class DL264 RD075 40K WH	2	80	4000	360	A	φ95*49.5,48	φ68-80	0.083
9290032593	DIAMOND CUT A Class DL264 RD090 30K WH	2.2	80	3000	400	A	φ105*49.5,48	φ80-90	0.099
9290032594	DIAMOND CUT A Class DL264 RD090 40K WH	2.2	80	4000	400	A	φ105*49.5,48	φ80-90	0.099



1

OFF

2

3

Terminal box not included; installation must be performed by a qualified person.

4

5

6

7

ON

Inrush Current

	9290032481 , 9290032588	9290032593 , 9290032594
Electrical characteristic		
I max(A)	15	18
Tref(μs)	0.06	0.07
MCB	Luminaire Max.(pcs)	
Type B-10A	98	64
Type B-16A	158	104
Type C-10A	164	109
Type C-16A	264	175

ATTENTION
OBSERVE PRECAUTIONS
FOR HANDLING
ELECTROSTATIC
SENSITIVE
DEVICES

01

Please read this manual before you start to install the luminaire.

02

The luminaire shall be installed by a qualified electrician and wired in accordance with the latest IEE electrical regulations of the national requirements.

03

Switch OFF the power supply before the installation or maintenance to avoid electrical shock.

04

The luminaire must not be used or stored in corrosive environment where hazardous materials such as Sulphur, Chlorine, Phthalates, etc., are present.

ATTENTION: In B manual, you will find all the explanations with numeric reference to the icons respectively in front of these safety instructions.



3241 659 88181
© 2022 Signify Holding
Signify

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. and are used under license